

LightPath 354115 | 9.2mm Dia., 0.54 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#16-691** 3-4 DAYS

[Other Coating Options](#)

-

1

+

€90,00

ADD TO CART

Qty 1-10
€90,00
Qty 11+
€79,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
9.20 ±0.015

Effective Focal Length EFL (mm):
6.75 @633nm

Numerical Aperture NA:

0.54
Substrate: D-ZK3
Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 633
Coating: BBAR (350-700nm)
Coating Specification: R _{avg} ≤0.5% @ 350 - 700nm
Surface Quality: 60-40
Clear Aperture CA (mm): 7
Edge Thickness ET (mm): 2.15
Center Thickness CT (mm): 4.08 ±0.02
f/#: 0.93
Bevel: Protective bevel as needed
Compatible Window: Thickness: 0.25 (t) (mm) Material: BK7
Lightpath Lens Code: 354115
Operating Temperature (°C): ≤200
Type: Aspheric Lens
Wavelength Range (nm): 350 - 700
Typical Applications: Collimate or Focus Laser Light
Working Distance (mm): 4.3
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant