

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

LightPath 354115 | 9.2mm Dia., 0.54 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#16-692** CLEARANCE ☐ **In Stock**

☐ [Other Coating Options](#)



1



€43,95

ADD TO CART

Qty 1+

€43,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
9.20 ±0.015

Effective Focal Length EFL (mm):
6.75 @ 633nm

Numerical Aperture NA:
0.54

Substrate: ☐
[D-ZK3](#)

Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 633
Coating: BBAR (600-1050nm)
Coating Specification: R _{abs} <1.0% @ 600 - 1050nm
Surface Quality: 60-40
Clear Aperture CA (mm): 7
Edge Thickness ET (mm): 2.15
Center Thickness CT (mm): 4.08 ±0.02
f#: 0.93
Bevel: Protective bevel as needed
Compatible Window: Thickness: 0.25 (t) (mm) Material: BK7
Lightpath Lens Code: 354115
Operating Temperature (°C): ≤200
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Typical Applications: Collimate or Focus Laser Light
Working Distance (mm): 4.3
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View