

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

SCHOTT GG-395, 25.4mm Dia., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#46-055** 3-4 DAYS



1



€38,75

ADD TO CART

Qty 1-10

€38,75

Qty 11+

€38,00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.40

Cut-Off Position λ_c (nm):
395±6

Cut-On Wavelength (nm): 395.00
Density (g/cm³): 2.55
Glass/Filter Number: SCHOTT GG395
Coating: Uncoated
Color: Clear
Passband Limit 1 λ_{p1} (nm): 480.00
Passband Limit 2 λ_{p2} (nm): 700.00
Spectral Transmittance t_p (%): 92.00
Stopband Limit λ_s(nm): 340.00
Surface Quality: 80-50
Transformation Temperature (°C): 538.00
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.38
Reflection Factor P_d: 0.92
Bevel: Protective as needed

Regulatory Compliance

Reach 191: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View