

LightPath 354120 | 4.99mm Dia., 0.15 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#16-689** **20+ In Stock**

⊖ 1 ⊕ €96³¹

ADD TO CART

Volume Pricing	
Qty 1-10	€96,31 each
Qty 11-49	€84,46 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

354120

Lightpath Lens Code:

Aspheric Lens

Type:

Typical Applications:

Collimate or Focus Laser Light

Physical & Mechanical Properties

Diameter (mm):

4.99 ±0.015

Clear Aperture CA (mm):

4.5

Edge Thickness ET (mm):

2.61

Center Thickness CT (mm):

2.92 ±0.03

Bevel:

Protective as needed

Optical Properties

Effective Focal Length EFL (mm):

15.04 @670nm

Numerical Aperture NA:

0.15

Substrate:

[D-ZK3](#)

Focal Length Tolerance (%):

±1

Aspheric Design Wavelength (nm):

670

Coating:

BBAR (350-700nm)

Coating Specification:

R_{avg} ≤0.5% @ 350 - 700nm

Surface Quality:

40-20

f/#:

3.33

Wavelength Range (nm):

350 - 700

Working Distance (mm):

13.19

Conjugate Distance:

Infinite

Transmitted Wavefront Error (λ, RMS):

<0.076

Environmental & Durability Factors

Operating Temperature (°C):

≤200

Regulatory Compliance

Certificate of Conformance:

[View](#)

PRODUCT DETAILS

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.

LASER OPTICS MADE BY EDMUND OPTICS®

[LEARN MORE](#)

TECHNICAL INFORMATION

