

[See all 67 Products in Family](#)

LightPath 354220 | 543nm Alignment, 0.25 NA Fiber Collimator w/ FC/APC Connector

See More by [Lightpath®](#)



Fiber Optic Collimator and Focuser Assemblies



Stock **#16-705** 4 In Stock

-

1

+

€349⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	€349,00 each
Qty 6+	€256,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
354220	Lightpath Lens Code:
Fiber Collimator	Type:

Physical & Mechanical Properties	
5.50	Clear Aperture CA (mm):
Protective as needed	Bevel:
304L Stainless Steel Housing	Construction:
11.00	Housing Diameter (mm):
22.43	Housing Length (mm):
Optical Properties	
11.00 @ 633nm	Effective Focal Length EFL (mm):
0.25	Numerical Aperture NA:
D-ZK3	Substrate: 
BBAR (350-700nm)	Coating:
Ravg <0.5% @ 350 - 700nm	Coating Specification:
40-20	Surface Quality:
2.00	f#:
350 - 700	Wavelength Range (nm):
Infinite	Conjugate Distance:
543	Alignment Wavelength (nm):

Hardware & Interface Connectivity	
FC/APC	Connector:

Threading & Mounting	
M11 x0.5	Mount:

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Easy to Integrate
 - Models for FC/PC, FC/APC, and SMA Connections Available
 - Four Wavelength Ranges Covering 350-1600nm
- LightPath® Fiber Optic Collimators are designed to collimate light exiting a fiber to a desired beam diameter or spot size or to focus light into a fiber when used in reverse. The lenses are diffraction limited, so they can achieve spot sizes down to a few microns. Lenses also feature an antireflection coating for low back reflection. LightPath® Fiber Optic Collimators are designed so that they can be used in pairs to couple the input and output light of optical devices. Optimum performance for long-term use is ensured by the factory set and tested lens alignment. Typical applications can include use with fiber coupled lasers and pigtailed receptacles, as well as communications and data transfer.

Technical Information

