

[See all 10 Products in Family](#)

## Glan-Thompson Polarizer 350 - 2200nm, 10mm



Glan-Thompson Polarizer

Stock #89-545 [CONTACT US](#)

⊖ 1 ⊕ €935.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€935,00 each
Qty 6+	€885,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Linear Polarizer **Type:**

### Physical & Mechanical Properties

10.0 **Clear Aperture CA (mm):**

25.40 **Diameter (mm):**

33.00 Length (mm):

Construction:  
Crystalline Glan-Thompson Polarizer

## Optical Properties

Coating:  
Single Layer MgF<sub>2</sub>

Extinction Ratio:  
<5 x 10<sup>-5</sup>

Substrate:   
Calcite

Surface Quality:  
20-10

Transmitted Wavefront, P-V:  
λ/2 @ 632.8nm

Beam Deviation (arcmin):  
<3

Transmitted Wavefront Distortion (RMS):  
λ/4 @ 632.8 nm

Wavelength Range (nm):  
350 - 2200

Damage Threshold, By Design:   
1 J/cm<sup>2</sup> @ 1064nm, 10ns, 10Hz

## Regulatory Compliance

RoHS 2015:  
[Compliant](#)


Certificate of Conformance:  
[View](#)

Reach 247:  
[Compliant](#)


## Product Details

- High Extinction Ratios up to 200 000:1
- High Laser Damage Thresholds up to 5 J/cm<sup>2</sup> @ 1064nm


Glan-Type Polarizers are mounted, polarizing prisms used in applications that require broad spectral ranges, high extinction ratios, or high polarization purities. Glan-Taylor Polarizers are medium-power, air-spaced UV to NIR polarizers that transmit the extraordinary beam. The ordinary beam is then reflected and absorbed by black glass plates that have been cemented to the prism. Glan-Laser Polarizers are similar to Glan-Taylor, but are designed for higher power applications and appropriate for use in Q-switched laser cavities. Glan-Laser Polarizers utilize an advanced polishing technique for minimizing surface scatter and feature two escape windows for passing the high power rejected light. Glan-Thompson Polarizers are low power polarizers that are ideal for UV, visible, or NIR applications, feature a cemented design, and transmit the extraordinary beam while absorbing the reflected ordinary beam.




## Technical Information



Glan-Taylor Polarizers



*Glan-Laser Polarizers*



*Glan-Thompson Polarizers*

;