

[See all 76 Products in Family](#)

LightPath 354525 | 6.65mm Dia., 0.44 NA, BBAR (350-700nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#19-701** **20+ In Stock**

-

1

+

€89^{.00}

ADD TO CART

Volume Pricing	
Qty 1-10	€89,00 each
Qty 11-49	€80,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads


General	
Compatible Window: Thickness: 0.25 (t) (mm) Material: BK7	
Lightpath Lens Code: 354525	
Typical Applications: Collimate or Focus Laser Light	

Physical & Mechanical Properties	
6.65 ±0.015	Diameter (mm):
5.75	Clear Aperture CA (mm):
1.82	Edge Thickness ET (mm):
3.02 ±0.03	Center Thickness CT (mm):
Protective as needed	Bevel:
4.25	Distance from Window to Lens (D) (mm):
Optical Properties	
6.70 @ 515nm	Effective Focal Length EFL (mm):
0.44	Numerical Aperture NA:
D-ZK3	Substrate: □
±1	Focal Length Tolerance (%):
BBAR (350-700nm)	Coating:
R _{avg} ≤0.5% @ 350 - 700nm	Coating Specification:
60-40	Surface Quality:
1.01	f/#:
350 - 700	Wavelength Range (nm):
4.9	Working Distance (mm):
Infinite	Conjugate Distance:
<0.05	Transmitted Wavefront Error (λ, RMS):
Environmental & Durability Factors	
≤200	Operating Temperature (°C):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:


Product Details

- Eliminate Spherical Aberration
- Multiple Coating Options Available
- Range of Numerical Apertures

LightPath® Geltech™ Molded Aspheric Lenses are used to eliminate spherical aberration and improve focusing and collimating accuracy in a variety of laser applications. Low NA aspheric lenses are designed to maintain beam shape, while high NA lenses gather all available light to maintain beam power over long distances. LightPath® Geltech™ Molded Aspheric Lenses are ideal for applications including sighting systems, bar code scanners, laser diode-to-fiber coupling, optical data storage, or biomedical lasers.



Technical Information



;