

LightPath 355615 | 2.05mm Dia., 0.20 NA, BBAR (600-1050nm), Molded Aspheric Lens

See More by [Lightpath®](#)



Precision Molded Aspheric Lenses

Stock **#16-694** CLEARANCE CONTACT US

[Other Coating Options](#)

⊖ 1 ⊕

€39,95

ADD TO CART

Qty 1+

€39,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
2.05 ±0.015

Effective Focal Length EFL (mm):
2.51 @ 1550nm

Numerical Aperture NA:
0.20

Substrate: ☐ [D-ZLaF52LA](#)

Focal Length Tolerance (%): ±1
Aspheric Design Wavelength (nm): 1550
Coating: BBAR (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Surface Quality: 40-20
Clear Aperture CA (mm): 1.01
Edge Thickness ET (mm): 1.22
Center Thickness CT (mm): 1.38 ±0.05
f#: 2.50
Bevel: Protective bevel as needed
Lightpath Lens Code: 355615
Operating Temperature (°C): ≤200
Type: Aspheric Lens
Wavelength Range (nm): 600 - 1050
Typical Applications: Collimate or Focus Laser Light
Working Distance (mm): 1.731
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant