

[See all 23 Products in Family](#)

GS3-U3-41C6NIR-C 1" FLIR Grasshopper®3 High Performance USB 3.0 NIR Camera

See More by [Teledyne FLIR](#)



Teledyne FLIR IIS Grasshopper®3 USB 3.0 Cameras (Front)



Stock **#89-526 6 In Stock**

[Similar Cameras](#)

-

1

+

€1.540⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.540,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

NIR	Spectrum:
General	
NIR Camera	Type:
	Model Number:

GS3-U3-41C6NIR-C	
FLIR	Manufacturer:
Grasshopper®3	Camera Series:
Physical & Mechanical Properties	
44 x 29 x 57.5 (excludes connectors and lens mount)	Dimensions (mm):
90	Weight (g):
Full	Housing:
Sensor	
128MB	Image Buffer:
1"	Sensor Format:
4.20	Resolution (Megapixels):
90.00	Frame Rate (fps):
2,048 x 2,048	Pixels (H x V):
5.5 x 5.5	Pixel Size, H x V (µm):
11.26 x 11.26	Sensing Area, H x V (mm):
CMOSIS CM4000	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
10 bit	Pixel Depth:
16µs - 7.03s	Exposure Time:
54.06	Dynamic Range (dB):
USB3 Vision v1.0	Machine Vision Standard:
Electrical	
4.5	Power Consumption (W):
Hardware & Interface Connectivity	
USB 3.0	Interface:
USB 3.1 Gen 1, Micro-B with Screw Locks	Connector:
Power over USB (required for operation) #86-770 or via GPIO with #86-784	Power Supply:
1 opto-isolated input, 2 opto-isolated outputs, 2 non-isolated bi-directional ports	GPIOs:
Hardware Trigger (GPIO) or Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
8-pin Hirose (HR25)	GPIO Connector Type:
5.00	Transfer Speed (Gbit/s):
Threading & Mounting	
C-Mount	Mount:
¼-20 with Tripod Mount Adapter #88-057	Mounting Threads:
Environmental & Durability Factors	

0 to +50	Operating Temperature (°C):
-30 to +60	Storage Temperature (°C):

Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 240:

Product Details

USB 3.0 cable (sold separately) is required for operation. Optional power supply ([#86-784](#)) available. Software available for [download](#).

- Feature High Resolution, High Sensitivity Sensors
- High Frame Rates Driven by USB 3.0 Interface
- Includes Image Capture Software and SDK



Teledyne FLIR IIS Grasshopper®3: Machine Vision area scan camera

The **Grasshopper®3** offers a cost-effective, powerful and easy-to-use alternative to Camera Link and dual GigE LAG solutions.

The **Grasshopper®3** camera line combines the benefits of CCD with the affordability and data throughput of either USB 3.0 or GigE interfaces. This high-performance camera model provides a range of characteristics with either CMOS or CCD sensors. Its FPGA and frame buffer-based architecture provides optimal reliability, a rich set of features, and a full image processing pipeline including color interpolation, gamma, and lookup table functionality.

Note: USB 3.0 cable (sold separately) is required for operation. Optional power supply ([#86-784](#)) available. Software available for [download](#). FLIR was previously known as Point Grey.

Features

- Compact form factor
- USB 3.0 models with resolutions from 2.3 to 12 Megapixel sensors
- GigE interface model at 2.3 Megapixel for high bandwidth performance
- Various high-resolution, large format CCD and CMOS sensor options
- Color transformation tools for true-to-life color
- GigE models feature PoE for simplified setup and maintenance
- Spinnaker SDK and code samples

Applications

- Factory automation
- 3D Measurement
- Flat Panel Inspection
- Life science instrumentation
- Biometrics kiosk solutions
- Ophthalmology
- Intelligent traffic systems