

## LS-WL1 Laser Driven White Light Source Kit



Fiber Coupled Laser-Driven White Light Source



Stock #23-881 **4 In Stock**

⊖ 1 ⊕ €3,415<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€3,415,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads



### General

LS-WL1 **Model Number:**

1 - 100% **Intensity Control Option:**

>10,000 **Lamp Lifetime (hours):**

**Note:**  
Software, power supply, USB cable, and 1mm core fiber are included.

#### Operating Modes:

**Constant output:** CW

**Stroboscope:** Frequency 0.12 Hz–200 kHz  
Duty cycle 0–100%

**Pulse trigger:** Pulse width: 10 $\mu$ s–4000ms  
Delay: 4 $\mu$ s–4000ms  
(Width + Delay  $\leq$  4000ms)

**Direct mode:** Analog/digital modulation to 100 kHz

**Note:** All modes allow output setting of 1–100%

## Physical & Mechanical Properties

#### Dimensions (mm):

125 x 110 x 60

#### Weight (kg):

0.45

## Optical Properties

#### Wavelength Range (nm):

440 - 750

## Electrical

#### Output Power (mW):

500mW from 1mm fiber (0.5NA)

#### Voltage (V):

12

#### Power Consumption (W):

20 @ 100% Power

## Hardware & Interface Connectivity

#### Connector:

SMA

#### Computer Interface:

RS232 via USB

## Regulatory Compliance

#### RoHS 2015:

[Compliant](#)

#### Certificate of Conformance:

[View](#)

#### Reach 233:

[Compliant](#)

## Product Details

- Extremely High Luminance with Output Power up to 500mW
- Light Coupling with 50 $\mu$ m – 1mm Core Diameter Multimode Fibers
- User-Friendly GUI for Remote Control via USB or RS-232
- 450 – 700nm Wavelength Range

Fiber Coupled Laser-Driven White Light Source utilizes a 450nm laser pumped stable ceramic phosphor converter to produce a highly efficient and extremely bright light source with output power up to 500mW from a 1mm fiber. Featuring a broad 450 – 700nm spectral output, this light source can achieve switching frequencies up to 200kHz to act as a high-frequency stroboscope. The switching frequency and duty cycle can be controlled either via the jog-wheel or through the user-friendly software interface. Fiber Coupled Laser-Driven White Light Source's highly efficient optical coupling is suitable for use with multimode fibers of 50 $\mu$ m to 1mm and an NA up to 0.50. The high-power white light is up to 100X higher luminance than white LEDs, has a 10,000 hour lifetime through highly efficient cooling, and features simple control via USB or RS-232. This light source is ideal for biomedical and imaging applications including excitation for fluorescence or chemical surface processing, high speed spectroscopy, and high-resolution microscopy.

**Note:** Software, power supply, USB cable, and 1mm core fiber are included.

## Technical Information



