

[See all 13 Products in Family](#)

M105 x 1.00 Mounted Linear Glass Polarizing Filter



Mounted Linear Glass Polarizing Filters

Stock #64-903 CLEARANCE **20+ In Stock**

€188⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€188,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Mounted Imaging Filter Type:

Physical & Mechanical Properties

99.00 Clear Aperture CA (mm):

110.00 +0/-0.2 Diameter (mm):

Construction:

Optical Properties

Uncoated **Coating:**

Approx. 19:1 at 400nm
Approx. 200:1 at 500nm
≥2700:1 at 550-650nm
Approx. 600:1 at 700nm

Float Glass **Substrate:** □

95% Efficiency **Polarization:**

Single: 30 **Transmission (%):**
Crossed: 0.15

400 - 700 **Wavelength Range (nm):**

Threading & Mounting

M105 x 1.00 **Filter Thread:**

9 ±0.1 **Mount Thickness (mm):**

11 **Mount Thickness Including Threads (mm):**

Environmental & Durability Factors

-15 to +70 **Operating Temperature (°C):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Stackable, Rotating Mount for Easy Integration into Imaging Systems
- Eliminate Hot Spots and Reduce Glare
- 95% Polarization Efficiency
- Also Available [Unmounted](#)

Mounted Linear Glass Polarizing Filters feature a rotatable threaded mount available in a wide range of standard thread sizes. Linear polarizing filters will transmit a single axis of polarization and can be used to reduce glare and hot spots in imaging systems. Two polarizing filters can be stacked to achieve a variable density effect. Thickness includes a 2mm male thread. Mounted Linear Glass Polarizing Filters have 95% polarization efficiency. The filters are also available [unmounted](#).

Technical Information

