

# IDS GV-5800SE-M-GL, GigE, 1" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ GigE Cameras



Stock #26-277 **2 In Stock**

- 1 + €1.000<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€1.000,00 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

## Product Downloads

Monochrome **Spectrum:**

## General

Monochrome Camera **Type:**

GV-5800SE-M-GL **Model Number:**

IDS Imaging Development Systems **Manufacturer:**

uEye+ SE **Camera Series:**

## Physical & Mechanical Properties

34 x 44 x 47 (excludes connectors and lens mount) **Dimensions (mm):**

106 **Weight (g):**

Full **Housing:**

## Sensor

128MB **Image Buffer:**

1" **Sensor Format:**

20.44 **Resolution (Megapixels):**

6.00 **Frame Rate (fps):**

5,536 x 3,692 **Pixels (H x V):**

2.40 x 2.40 **Pixel Size, H x V (µm):**

13.286 x 8.861 **Sensing Area, H x V (mm):**

Sony IMX183 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Rolling **Shutter Type:**

12 bit **Pixel Depth:**

0.17ms - 2000ms **Exposure Time:**

71.00 **Dynamic Range (dB):**

GigE Vision **Machine Vision Standard:**

## Electrical

2 - 3.2 **Power Consumption (W):**

## Hardware & Interface Connectivity

GigE (PoE) **Interface:**

GigE RJ45, screwable **Connector:**

Power over Ethernet (PoE) or 12 - 24VDC via GPIO with [#16-016](#) **Power Supply:**

2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Voltage Output, 1 Ground **GPIOs:**

Hardware Trigger (GPIO); Software Trigger **Synchronization:**

Back Panel **Interface Port Orientation:**

8-pin Hirose connector (HR25-7TR-8PA(73)) **GPIO Connector Type:**

## Threading & Mounting

C-Mount **Mount:**

¼-20 with Tripod Mount Adapter [#16-017](#) **Mounting Threads:**

## Environmental & Durability Factors

0 to +55 **Operating Temperature (°C):**

**Storage Temperature (°C):**

## Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **REACH 241:**

## Product Details

- Standard (SE) and Compact (CP) Housing Options Available
- C-Mount with Large Format CMOS Sensors up to 1.1"
- GenICam GigE Vision Compliant
- [IDS Imaging uEye CP/XCP/SE USB3 Cameras](#) Available

IDS Imaging uEye CP/SE GigE Cameras utilize IDS Imaging's [peak SDK platform](#) that supports GenICam and GigE Vision standards for ease of software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat sensitive applications. IDS Imaging uEye CP/SE GigE Cameras feature a screwable 8-pin Hirose connector for trigger and flash as well as two GPIOs. These cameras are ideal for a variety of applications such as automation, automotive, medical technology, and logistics.