

[See all 33 Products in Family](#)

## IDS U3-3276LE-C-HQ, USB 3.0, 1/1.8" Color Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye LE/XLE Camera (M12, Full Housing, Front View)



Stock #24-108 **1 In Stock**

[Similar Cameras](#)

- 1 + €520.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€520,00 each
Need More?	<a href="#">Request Quote</a>

Prices shown are exclusive of VAT/local taxes

### Product Downloads

Color

Spectrum:

### General

Color Camera

Type:

Model Number:

**Manufacturer:**  
IDS Imaging Development Systems

**Camera Series:**  
uEye+ LE

## Physical & Mechanical Properties

**Dimensions (mm):**  
47 x 46 x 25 (excludes connectors and lens mount)

**Weight (g):**  
37

**Housing:**  
Full

## Sensor

**Image Buffer:**  
Not Specified

**Sensor Format:**  
1/1.8"

**Resolution (Megapixels):**  
3.15

**Frame Rate (fps):**  
58.00

**Pixels (H x V):**  
2,056 x 1,542

**Pixel Size, H x V (µm):**  
3.45 x 3.45

**Sensing Area, H x V (mm):**  
7.093 x 5.32

**Imaging Sensor:**  
Sony IMX265

**Type of Sensor:**  
Progressive Scan CMOS

**Shutter Type:**  
Global

**Pixel Depth:**  
12 bit

**Exposure Time:**  
0.025ms - 1900ms

**Dynamic Range (dB):**  
70.00

**Machine Vision Standard:**  
USB3 Vision

## Electrical

**Power Consumption (W):**  
1 - 2

## Hardware & Interface Connectivity

**Interface:**  
USB 3.0

**Connector:**  
USB Type-C

**Power Supply:**  
Power over USB

**GPIOs:**  
N/A

**Synchronization:**  
Hardware Trigger (GPIO); Software Trigger

**Interface Port Orientation:**  
Back Panel (Right Angle)

**GPIO Connector Type:**  
No GPIO Connector Available

## Threading & Mounting

**Mount:**  
S-Mount (M12 x 0.5)

**Mounting Threads:**  
1/4-20 with Tripod Mount Adapter [#16-017](#)

## Environmental & Durability Factors

**Operating Temperature (°C):**  
0 to +55

**Storage Temperature (°C):**  
-20 to +80

## Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **REACH 241:**

## Product Details

- Up to 8.0MP Resolution with Framrates up to 230fps
- Board Level Options with C/CS-Mount or S-Mount Available
- GenICam USB3 Vision Compliant

IDS Imaging uEye LE/XLE USB3.1 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GenICam and USB3 Vision standards for ease of software development and integration. These cameras are available in board-level or housed options with S-Mount or C/CS-Mount versions. The C/CS-Mount configurations come with a 5mm spacer to easily adapt between C-Mount and CS-Mount lenses. IDS Imaging uEye LE/XLE USB3.1 Cameras are ideal for small device construction, medical technology, robotics, and machine vision applications. With a compact design, the XLE version is suitable for integration into embedded systems whereas the LE version is suitable for small device projects.