

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

LightPath 390036 | 6.5mm Dia., 0.56 NA, BBAR (3000-5000nm), Mounted IR Aspheric Lens

See More by [Lightpath®](#)



Stock #66-569 CLEARANCE 3-4 DAYS
[Other Coating Options](#)



1



€160,95

ADD TO CART

Qty 1+

€160,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
6.50 ±0.10

Effective Focal Length EFL (mm):
4.00 @ 2500nm

Numerical Aperture NA:
0.56

Substrate: ☐
Black Diamond™ BD-2 (Ge₂₈Sb₁₂Se₆₀)

Aspheric Design Wavelength (nm): 2500
Coating: BBAR (3000-5000nm)
Coating Specification: R _{avg} <1.0% @ 3 - 5μm
Surface Quality: 80-50
Clear Aperture CA (mm): 5.00
Center Thickness CT (mm): 2.50
f/#: 0.89
Bevel: Protective bevel as needed
Density (g/cm³): 4.68
Index of Refraction n_d @ 10μm: 2.6023
Index of Refraction n_d @ 14μm: 2.5843
Index of Refraction n_d @ 4μm: 2.6210
Index of Refraction n_d @ 5μm: 2.6173
Lightpath Lens Code: 390036
Mount: Stainless Steel, MØ x0.5 Thread
Thermo-optic coefficient dn/dT: 70 x 10 ⁻⁶ /°C from -40° to +80°C (5 - 14 μm)
Transformation Temperature (°C): 285.00
Type: Aspheric Lens
Wavelength Range (nm): 3000 - 5000
Working Distance (mm): 3.05
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant