


[All Products](#) / [Optics](#) / [Diffraction Gratings](#) / [Coherent® LightSmyth™ Transmission Diffraction Gratings](#)

[See all 16 Products in Family](#)

Coherent® LightSmyth™ Transmission Diffraction Grating, 31.8 x 12.3mm Transm

See More by [Coherent®](#)



LightSmyth™ Transmission Diffraction Gratings

Stock #16-863 **1 In Stock**

1

€695^{.00}

ADD TO CART

Volume Pricing	
Qty 1-9	€695,00 each
Qty 10-24	€625,50 each
Need More?	Request Quote

Product Downloads	
STEP:step	Curve:pdf
PDF Drawing:pdf	IGES:igs
Spec Sheets	eDrawing:eprt
EO Spec Sheet	

Prices shown are exclusive of VAT/local taxes

General

Model Number:	1304192	Type:	Transmission Diffraction Grating
Note:	S-Polarization defined with E-field parallel to the grating grooves		

Physical & Mechanical Properties

Groove Density Uniformity (grooves/mm):	0.001	Dimensions (mm):	31.80 x 12.30
Clear Aperture CA (mm):	30.80 x 11.30	Construction:	Multi-Layer Dielectric Binary Etch Grating
Length (mm):	31.80	Thickness (mm):	0.95 ±0.050
Width (mm):	12.30	Alignment of Grooves to Edge (°):	0.1 (typical)

Optical Properties

Groove Density (grooves/mm):	1600	Design Wavelength DWL (nm):	1030 ±10
Minimum Efficiency (%):	≥94 @ 1030nm	Angle of Incidence (°):	55.5 ±1
Coating:	Dielectric	Substrate:	Fused Silica (Corning 7980)

Surface Quality: 60-40

Polarization: S

Regulatory Compliance

Certificate of Conformance: [View](#)

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- High Diffraction Efficiency ($\geq 90\%$ Absolute) and Low Scatter
- Polarization Independent and Single Polarization Optimized Gratings
- Robust Inorganic Materials for Superior Power Handling and Reliability
- Designs for NIR Wavelengths between 800 - 1800nm

Coherent® LightSmyth™ Transmission Diffraction Gratings are manufactured through a precision lithographic wafer-scale fabrication process and provide excellent optical performance, low polarization sensitivity, and low scatter. These gratings have a high diffraction efficiency of $\geq 90\%$, minimizing optical losses when used in multi-pass configurations. Gratings designed for near infrared (NIR) wavelengths between 800 - 1800nm are available with all featuring a precision line density uniformity of 0.001 lines/mm. Coherent® LightSmyth™ Transmission Diffraction Gratings are used in demanding applications including Spectral Beam Combining (SBC), LiDAR, optical telecommunications, pulse compression of pico- and femtosecond pulses, and spectroscopy. These gratings contain no organic materials and can be used with high power lasers and in environments up to 500 °C with no effects on performance. Please contact us for custom sizes or OEM requirements.

Note: II-VI Incorporated is now Coherent Corp.

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.




Component Handling Tools

Related Products



Transmission Gratings




UltraFast Innovations (UFI)
Third Order Dispersion (TOD)
Ultrafast Mirrors



Fixed Filter Mounts

Frequently Purchased Together



#47-239 - 50mm, Protected Gold, N-BK7 Right Angle Prism Mirror (Leg Coated)
€443,00

Qty



#34-409 - 25mm NIR I, N-BK7 Right Angle Prism (Hypotenuse Coated)


€119,00

Qty



€128,00

Qty



#34-409 - 25mm NIR I, N-BK7 Right Angle Prism (Hypotenuse Coated)
€167,00

Qty

Please select your shipping country to view the most accurate inventory information, and to determine the correct Edmund Optics sales office for your order.

Select Your Country/Region:

Resources

Media Type

- Application Note
- Video
- FAQ
- Glossary

WEBINARS

Helpful Tips for Selecting the Correct Diffraction...

APPLICATION NOTE

All About Diffraction Gratings

VIDEO

Richardson Gratings™ Unboxing

? FAQ

What is the difference between holographic...

? FAQ

How do the efficiency curves relate to the actual...

? FAQ

What is the difference between Rowland circl...

[View More](#)