

[See all 14 Products in Family](#)

LightPath 390037 | 5.5mm Dia., 0.85 NA, BBAR (1800-3000nm), Molded IR Aspheric Lens

See More by [Lightpath®](#)



Stock **#66-564** CLEARANCE **1 In Stock**

☐ [Other Coating Options](#)

-

1

+

€250⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€250,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
390037	Lightpath Lens Code:
Aspheric Lens	Type:

Physical & Mechanical Properties	
5.50 ±0.015	Diameter (mm):

4.00	Clear Aperture CA (mm):
2.24	Edge Thickness ET (mm):
3.00	Center Thickness CT (mm):

Protective as needed	Bevel:
----------------------	--------

Optical Properties

1.87 @ 9500nm	Effective Focal Length EFL (mm):
---------------	----------------------------------

0.85	Numerical Aperture NA:
------	------------------------

Black Diamond™ BD-2 (Ge ₂₆ Sb ₁₂ Se ₆₀)	Substrate: ☐
---	-------------------------------------

9500	Aspheric Design Wavelength (nm):
------	----------------------------------

BBAR (1800-3000nm)	Coating:
--------------------	----------

R _{avg} <1.0% @ 1.8 - 3.0μm	Coating Specification:
--------------------------------------	------------------------

80-50	Surface Quality:
-------	------------------

0.58	f/#:
------	------

2.6023	Index of Refraction (n _d) @ 10μm:
--------	---

2.5843	Index of Refraction (n _d) @ 14μm:
--------	---

2.6210	Index of Refraction (n _d) @ 4μm:
--------	--

2.6173	Index of Refraction (n _d) @ 5μm:
--------	--

1800 - 3000	Wavelength Range (nm):
-------------	------------------------

0.72	Working Distance (mm):
------	------------------------

Infinite	Conjugate Distance:
----------	---------------------

Material Properties

4.68	Density (g/cm ³):
------	-------------------------------

70 x 10 ⁻⁶ /°C from -40° to +80°C (5 - 14 μm)	Thermo-optic coefficient dn/dT:
--	---------------------------------

285.00	Transformation Temperature (°C):
--------	----------------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Compliant	Reach 233:
---------------------------	------------

Product Details

- Wavelength Range of 1.8 - 12μm
- Variety of Coating Options
- Mounted and Unmounted Versions

LightPath® Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses feature a low-cost, molded design and offer several key benefits over Germanium substrate aspheres. With a dn/dT and CTE significantly less than that of Germanium, the lenses feature a smaller change in focal length as a function of temperature change. Featuring a higher operating temperature than Germanium (which suffers 20 – 30% transmission loss at 100°C), the lenses can be used in applications including collimators for QCL lasers and as components within thermal imaging assemblies. LightPath Mid-Wave and Long-Wave Infrared (IR) Aspheric Lenses have a wavelength range of 1.8 - 12μm. These lenses are available mounted or unmounted, in a variety of coating options.

Technical Information



;