

Mounted Window for 800nm, 0.80 NA, aplanoXX Aplan Objective

See More by [AdlOptica](#)



Mounted Window

Stock **#19-496** [CONTACT US](#)

-

1

+

€280^{,00}

ADD TO CART

Volume Pricing	
Qty 1+	€280,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Model Number:	Window in Holder L9333.06 (+D12 800)
Type:	Mounted Window
Note:	Protective window for #19-492
Physical & Mechanical Properties	

4.40	Length (mm):
8	Clear Aperture CA (mm):
29.50	Diameter (mm):
Optical Properties	
800	Design Wavelength DWL (nm):
770 - 900	Wavelength Range (nm):
25 mJ @ 5ns	Damage Threshold, By Design: ☐
25 mJ @ 5ns	Damage Threshold, Pulsed:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

Product Details

- Aplanatic Optical Design
- High Numerical Aperture for Small Spot Sizes
- Designs for 800 and 1030nm with Focusing Depth Up to 4mm
- [AdlOptica foXXus Multi-Focus Objectives](#) Also Available

AdlOptica aplanoXX Aplan Objectives compensate for spherical aberration and coma when focusing into glass, sapphire, silicon carbide, silicon, PMMA, and other transparent materials at depths up to 4mm. These objectives are designed to be used with ultrafast solid-state and fiber lasers and are optimized for 800nm (Ti:sapphire) and 1030nm (Yb:doped). Featuring C-Mount threading and an optical design insensitive to misalignment, these objectives are easy to integrate into laser systems. AdlOptica aplanoXX Aplan Objectives are ideal for micromachining glass, 3D nanofabrication, waveguide recording, and selective laser etching. A collar on the objective allows for manual adjustment of focus and a replaceable front window protects from debris during materials processing.

Technical Information

