

[See all 10 Products in Family](#)

Nikon Type N 8ml PCB Free Immersion Oil

See More by [Nikon](#)



Stock **#75-380** NEW [CONTACT US](#)

- 1 + €15⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€15,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes


Product Downloads	
General	
Nikon	Manufacturer:
Optical Properties	
1.518	Index of Refraction (n _d):
41	Abbe Number (v _d):
Environmental & Durability Factors	
23	Operating Temperature (°C):

Product Details

- Superior UV Transmission
- High Numerical Aperture Designs
- Feature Low Auto-Fluorescence Materials

Nikon CFI Super Fluor Objectives are designed to provide superior transmission to ultraviolet applications operating down to 340nm, including for use with fluorochromes indo-1, fura-2, and fluo-3, or for photo-activation of caged compounds. Nikon CFI Super Fluor Objectives are designed using low auto-fluorescence materials along with high numerical apertures to guarantee sharp, bright fluorescence images. These microscope objectives have been optimized for improved signal-to-noise ratios at short wavelengths.

Technical Information



Dimensions (mm)						
Stock No.	Magnification	Parafoval Length	A	B	C	D
#88-374	4X	60.06	30.0	44.4	19.7	M25 x0
#88-375	10X	60.06	32.0	58.7	8.0	M25 x0
#88-376	20X	60.06	33.5	58.9	9.0	M25 x0
#88-377	40X	60.06	33.0	59.6	7.5	M25 x0