

## NIST Traceable Longwave Sensor, 335 - 380nm



#88-136 with NIST Traceable Sensor

Stock **#88-139 1 In Stock**

⊖ 1 ⊕ €550<sup>00</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €550,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### Physical & Mechanical Properties

Accuracy (%):  
±5

### Optical Properties

Wavelength Range (nm):  
335 - 380

Calibration Wavelength (nm):  
365.00

Certificate of Conformance:

[View](#)

---

## Product Details

- Designed to Detect UV Wavelengths from 250 – 380nm
- NIST Certified Sensors
- 9V Battery Provides up to 120 Hours of Operation
- Requires One NIST Traceable Sensor for Operation

The NIST Certified UV Radiometer is ideal for inspecting ultraviolet light sources in a variety of quality control applications. The NIST Certified UV Radiometer is powered by a standard 9V battery for up to 120 hours of operation. Three NIST certified interchangeable sensors are available to detect a wide range of ultraviolet wavelengths from 250 – 380nm. The NIST Certified UV Radiometer's range switch allows the selection of three intensity ranges.

**Note:** The UV Radiometer Unit ([#88-136](#)) requires one NIST Traceable Sensor ([#88-137](#), [#88-138](#), or [#88-139](#)) for operation.

---