

Ocean Optics HR2 NIR High Resolution Spectrometer

See More by [Ocean Optics](#)



Stock #90-024 NEW **1 In Stock**

€4.962⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€4.962,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

OceanDirect & OceanView

Software:

1µs - 2s

Integration Time:

HR-2N750-25

Model Number:

Note:
Includes manual QR code, software QR code, calibration reports for wavelength and linearity, 1 m USB cable

SMA905	Input Port Termination:
	Grating: Ruled Diffraction Grating: 1200 Grooves/mm, Blazed @ 750nm
Cross Czerny Turner	Optical Bench:
Physical & Mechanical Properties	
25	Slit Width (µm):
0.9306	Weight (kg):
149.0 x 106.4 x 48.2	Dimensions (mm):
Optical Properties	
0.24	Spectral Resolution (nm):
750 - 900	Wavelength Range (nm):
Sensor	
CCD	Type of Sensor:
Electrical	
Single Scan @ 10 ms: 380:1 Max per second with High Speed Averaging Mode: 25,800:1	Signal to Noise S/N Ratio:
Hardware & Interface Connectivity	
USB, RS-232	Computer Interface:
Threading & Mounting	
(3) 2-56	Mounting Threads:
Environmental & Durability Factors	
0 to +55	Operating Temperature (°C):
-30 to +70	Storage Temperature (°C):
0.02 nm/°C	Thermal Stability:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

Product Details

- High Resolution Spectrometers for Narrow Peak Identification
- Spectral Ranges Spanning UV-VIS, VIS-NIR, and NIR Wavelengths
- Rapid Acquisition Speed and Excellent Thermal Stability

Ocean Optics HR High Resolution Spectrometers, available in HR2, HR4, and HR6 models, are designed to identify narrow spectral peaks with detailed spectral analysis for applications that require high-resolution solutions. The HR2 spectrometers feature high-resolution performance, fast scan speeds, and excellent thermal stability, providing rapid, real-time results ideal for applications such as plasma monitoring and pharmaceutical analysis. The HR4 spectrometers combine high-resolution spectral analysis with excellent thermal stability, making these models excel in precision-demanding environments such as DNA/RNA analysis, biomedical research, and high-throughput reflection testing. The HR6 spectrometers offer high sensitivity, high resolution, and excellent signal-to-noise ratio (SNR) performance for applications including protein absorbance and emission of broadband sources. The Ocean Optics HR High Resolution Spectrometers include the user-friendly OceanView software system to optimize spectrometer performance, ease system integration, and access data for analysis.