

Ocean Optics SR2 UV-VIS Spectrometer

See More by [Ocean Optics](#)



Stock #90-018 NEW **1 In Stock**

⊖ 1 ⊕ €3.859⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€3.859,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

OceanDirect & OceanView **Software:**

1 μs – 2 s **Integration Time:**

SR-2UW300-25 **Model Number:**

Note:
Includes manual QR code, software QR code, calibration reports for wavelength and linearity, 1 m USB cable

SMA905	Input Port Termination:
Ruled Diffraction Grating: 600 Grooves/mm, Blazed @ 300nm	Grating:
Cross Czerny Turner	Optical Bench:
Physical & Mechanical Properties	
25	Slit Width (µm):
0.275	Weight (kg):
88.1 x 63.5 x 31.45	Dimensions (mm):
Optical Properties	
1.33	Spectral Resolution (nm):
195 - 850	Wavelength Range (nm):
Sensor	
CCD	Type of Sensor:
Electrical	
Single Scan @ 10 ms: 380:1 Max per second with High Speed Averaging Mode: 25,800:1	Signal to Noise S/N Ratio:
Hardware & Interface Connectivity	
USB, RS-232	Computer Interface:
Threading & Mounting	
(3) 4-40	Mounting Threads:
Environmental & Durability Factors	
0 to +55	Operating Temperature (°C):
-30 to +70	Storage Temperature (°C):
0.02 nm/°C	Thermal Drift:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

Product Details

- Compact Design and Powerful Performance
- Broad Wavelength Range Options Spanning 180 - 1040nm
- Three Models Available for a Diverse Range of Applications

Ocean Optics SR Versatile Spectrometers are available in S2, S4, and S6 models, each of which offers high performance and broad spectral coverage to suit a diverse set of applications. SR2 spectrometers are optimized for fast spectral acquisition and high signal-to-noise ratio (SNR), making them ideal for applications such as laser characterization, plasma monitoring, and absorbance concentration. The SR4 spectrometers present superior thermal wavelength stability, low-noise CCD detection, and consistent high signal-to-noise performance, perfect for plasma monitoring and reflection measurements. High-sensitivity SR6 models provide exceptional SNR and UV response, supporting applications such as UV absorbance, fluorescence, and plasma diagnostics. The Ocean Optics SR Versatile Spectrometers include the user-friendly OceanView software system to optimize spectrometer performance, ease system integration, and access data for analysis.