

[See all 21 Products in Family](#)

Oryx® ORX-10GS-89S6C-C Color 10GigE

See More by [Teledyne FLIR](#)



ORYX-10G-310S9C



Stock #19-793 **1 In Stock**

- 1 + €4.310⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€4.310,00 each
Need More?	Request Quote

Product Downloads

Color **Spectrum:**

General

Color Camera **Type:**

ORX-10GS-89S6C-C **Model Number:**

FLIR **Manufacturer:**

Oryx® **Camera Series:**

Physical & Mechanical Properties

60 x 60 x 64 **Dimensions (mm):**

386 **Weight (g):**

Full **Housing:**

Sensor

240MB **Image Buffer:**

1" **Sensor Format:**

8.90 **Resolution (Megapixels):**

93.00 **Frame Rate (fps):**

4,096 x 2,160 **Pixels (H x V):**

3.45 x 3.45 **Pixel Size, H x V (µm):**

14.13 x 7.46 **Sensing Area, H x V (mm):**

Sony IMX255 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

8/10/12 Bit **Pixel Depth:**

5µs - 30s **Exposure Time:**

71.57 **Dynamic Range (dB):**

GigE Vision **Machine Vision Standard:**

Electrical

12.6 **Power Consumption (W):**

Hardware & Interface Connectivity

10GigE **Interface:**

GigE interface with Screw Locks **Connector:**

Power Supply:
Power Supply Required and Sold Separately.
USA: [#19-803](#)
Europe: [#19-803](#)
Japan: [#19-803](#)
Korea: Not Available
China: [#19-803](#)

GPIOs:
2 opto-isolated inputs, 2 opto-isolated outputs, 2 non-isolated bi-directional

Synchronization:

Hardware Trigger (GPIO) or Software Trigger

Back Panel

Interface Port Orientation:

GPIO Connector Type:

12-pin Hirose (HR10)

Threading & Mounting

C-Mount

Mount:

Mounting Threads:
1/4-20 with Tripod Mount Adapter [#19-804](#)

Environmental & Durability Factors

Operating Temperature (°C):
0 to +70

Storage Temperature (°C):
-30 to +60

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- 10GBASE-T (10GigE) Ethernet Interface
- 3.2 to 31 Megapixel Sony 4th Gen Pregius S Sensors
- Supports 4K60, 12-bit System Integration
- Tripod Adapter Built into Larger Oryx® Models



Teledyne FLIR IIS Oryx 10GigE: High throughput, Award-winning camera designs

Reliably capture images at high speed

The **Oryx 10GigE** camera family supports transfer speeds of up to 10 Gbit/s enabling capture of 4K resolution, 12-bit images at speeds exceeding 60 FPS. Reliable image transfer at high bandwidth is further improved with Myricom bundles and packet resend feature. A range of sensor options offer resolutions from 3.2 Megapixel up to 31 Megapixel. Oryx features include IEEE1588 clock synchronization and full compatibility with several popular third-party software supporting GigE Vision. Oryx's 10GBASE-T interface is a proven and widely deployed standard that provides reliable image transfer at cable lengths over 50 meters on inexpensive CAT6A, and up to 30 meters on CAT5e.

Note: The ORX-10G-310S9 and ORX-10G-245S8 cameras require an F-Mount lens adapter (sold separately).

Features

- Color or monochrome sensors
- Various frame triggering options including up to 8 sets of 2-feature sequencer
- Pixel binning, decimation, ROI
- On camera image processing includes Gamma, LUT, and sharpness

Applications

- Stadium venues
- Site security
- Factory automation
- Traffic monitoring
- Inspection systems