

Micro HM Objective



ROBUSTO™ and ROBUSTO-Lite™ Cinematography Lenses



Stock **#16-114** **1 In Stock**

-

1

+

€1.470⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.470,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

Numerical Aperture (NA) Range:

0.306 - 0.035

General

Type:

Lens Accessory

Physical & Mechanical Properties

Length (mm):

74.50	
Optical Properties	
18 - ∞	Working Distance (mm):
0X- 16X	Magnification:
Threading & Mounting	
C-Mount	Mounting Threads:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- Exceptional Micro, Macro, and Long-Distance Performance
 - Enable Long Distance Imaging with Superior Detail over Depth of Field
 - Six Interchangeable Objectives to Meet Application Requirements
- ROBUSTO™ Cinema Production Lenses, part of Infinity Photo-Optical Company's line of Nelsonian™ Optics, incorporate Infinity's world-renowned long working distance microscope technology to provide exceptional performance for micro, macro, and long-distance cinema production and advanced photography applications. These lenses have focus and iris adjustment and are available in two models: the ROBUSTO™ or the ROBUSTO Lite™. The ROBUSTO is designed with built in gearing for focus motorization while the ROBUSTO Lite features a smaller, more lightweight body for easy manual use with an optional gear for motorization available. Both versions of the ROBUSTO lens utilize one of six interchangeable objectives to meet application requirements. In addition to their use in cinema production and photography applications, ROBUSTO Cinematography Lenses are also ideal for industrial, forensic, and biological applications where they can transform any machine vision camera into a portable, continuously-focusable microscope.
- Visit the [Infinity Photo-Optical Cinema Products](#) brand page to learn more about these products!