

TECHSPEC<sup>®</sup> Mounting Clamp, 160mm Inner Diameter



Mounting Clamp, 160mm Inner Diameter

Stock **#56-873** 20+ In Stock

-

1

+

€500<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | €500,00 each                  |
| Need More?     | <a href="#">Request Quote</a> |

**i** Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Lens Accessory

Physical & Mechanical Properties

Inner Diameter (mm):

160

Optical Properties

Lens Wavelength Range:

VS


| Regulatory Compliance |                                    |
|-----------------------|------------------------------------|
| Not Compliant         | <b>RoHS 2015:</b>                  |
| Not Compliant         | <b>Reach 223:</b>                  |
| <a href="#">View</a>  | <b>Certificate of Conformance:</b> |

## Product Details

- High Resolution Telecentric Lens for Measurement and Gauging
- Up to 5 MegaPixels, 3.45µm Pixel Size Sensors
- Up to 2/3", C-Mount Telecentric Lens
- Magnification from 0.06X to 1X


TECHSPEC® GoldTL™ Telecentric Lenses were designed specifically for machine vision and metrology applications. The unique focusable design allows for working distance adjustment, while still providing <0.2° telecentricity. These lenses also feature high resolutions, low distortions, and are available for 1/2" or 2/3" sensors. TECHSPEC® GoldTL™ Telecentric Lenses have a front filter thread for easy integration of [color filters](#), [polarizers](#) or other mounted components. Both the iris and focusing adjustment positions can be fixed by set screws to remain secure in high vibration environments.

## Technical Information




0.08X &amp; 0.06X Telecentric Lens Units: mm

Units: mm




1X &amp; 0.73X Telecentric Lenses Units: mm

Units: mm



### 0.5X & 0.36X Telecentric Lenses



0.25X &amp; 0.18X Telecentric Lenses Units: mm

Units: mm

| Stock No. | A     | B      | C      | D     | E     | F       | G      |
|-----------|-------|--------|--------|-------|-------|---------|--------|
| #56-024   | 88mm  | 16mm   | 34mm   | 94mm  | 120mm | 101.6mm | 50mm   |
| #56-025   | 85mm  | 17.5mm | 32.5mm | 91mm  | 120mm | 101.6mm | 48.5mm |
| #56-026   | 103mm | —      | 39.5mm | 107mm | 103mm | 90mm    | 55.5mm |
| #56-027   | 134mm | —      | 55mm   | 148mm | 134mm | 122mm   | 81mm   |

