

[See all 12 Products in Family](#)

# Red, Ethernet High Intensity Coaxial Spot Light

See More by [Advanced Illumination](#)



Stock #21-360 [CONTACT US](#)

⊖ 1 ⊕ €565<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€565,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

## Product Downloads

### General

SL162-625C1 **Model Number:**

50,000 **LED Lifetime (hours):**

1 **Number of LEDs:**

**Type of Illumination:**

**Note:**

Required Controller [#18-645](#); Required Power Supply [#66-855](#)

**Manufacturer:**

Advanced Illumination

**Geometry:**

Spot Light

**Illumination Mode:**

Constant, Pulsed, Gated

## Physical & Mechanical Properties

**Weight (g):**

85.1

## Optical Properties

**Color:**

Red

**Wavelength (nm):**

625

## Hardware & Interface Connectivity

**Connector:**

C1

**Power Supply:**

Power Supply Required and Sold Separately.

USA: [#66-855](#)

Europe: [#66-855](#)

Japan: [#89-513](#)

Korea: [#33-773](#)

China: [#66-855](#)

**Length of Cable (m):**

2

## Environmental & Durability Factors

**Operating Temperature (°C):**

0 to +60

## Regulatory Compliance

**RoHS 2015:**

[Exempt](#)

**Reach 224:**

[Contains SVHC\(s\)](#)

**Certificate of Conformance:**

[View](#)

## Product Details

- Controllable via Ethernet GUI or Web Browser
- Compatible with 8mm or 1/4" (0.312") Fiber Illumination Ports
- Efficient Thermal Management for Long LED Life
- Compatible with [TECHSPEC® Telecentric Backlight Illuminators and Lenses](#)

Advanced Illumination Ethernet Controlled High Intensity In-Line Lights utilize a C1 connector to connect to the DCS-100E Single Output Controller ([#18-645](#)). The DCS-100E Single Output Controller allows these high intensity in-line lights to be ethernet controlled through a downloadable software package or through a Web Based Graphical User Interface (GUI). With efficient thermal management, these in-line lights are able to provide 33,000 Lux at a working distance of 100mm with a spot size of 61mm in either a continuous, pulsed, or gated operating mode. Advanced Illumination Ethernet Controlled High Intensity In-Line Lights can be overdriven in short pulses without damaging the LED through Advanced Illumination's SignaTech™ Control System which is available with the DCS-100E Controller. These lights are available in UV, Blue, Green, Red Orange, IR, or White and are compatible with the 8mm port found on many in-line illumination imaging lenses, making them an excellent choice for use with TECHSPEC® Telecentric Backlight Illuminators and telecentric lenses with an [inline illumination port](#). For applications that do not require ethernet controlled functionality, [Advanced Illumination High Intensity In-Line Lights](#) are also available.

**Note:** 24V power supply ([#66-855](#)) and DCS-100E Single Output Controller ([#18-645](#)) are required for use.