

TECHSPEC[®] NUV M62.0 x 0.75 High Performance Machine Vision Filter



TECHSPEC[®] High Performance Mounted Machine Vision Filters

Stock **#89-762** 2 In Stock

-

1

+

€439⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	€439,00 each
Qty 10+	€404,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
OD ≥3.0 @ 400 - 650nm OD ≥4.0 @ 200 - 250nm	Note:
Mounted Imaging Filter	Type:
Physical & Mechanical Properties	
57.5	Clear Aperture CA (mm):

Mounted in Black Anodized Ring	Construction:
65.00	Outer Diameter (mm):
1.75 ±0.10	Substrate Thickness (mm):

Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2
--

Optical Properties
Blocking Wavelength Range (nm): 200-250, 400-650
Coating: Hard Coated
Color: NUV
Center Wavelength CWL (nm): 325.00
Full Width-Half Max FWHM (nm): 106.00
Optical Density OD (Average): ≥3.0
Wavelength Range (µm): 0.2 - 1.2
Average Transmission (%): ≥75

Threading & Mounting
Filter Thread: M62 x0.75
Mount Thickness (mm): 5.5
Mount Thickness Including Threads (mm): 8.0

Environmental & Durability Factors
Environmental Durability: Humidity per ML-STD-810H, Section 507.6 Temperature per ML-STD-810H, Section 501.7 and 502.7


Regulatory Compliance
Certificate of Conformance: View



Product Details

- Optimized for Use with Popular LEDs
- Multiple Mounting Sizes and Threads Available to Ease System Compatibility
- Extremely High and Flat Transmission Profiles Provide Even Illumination

TECHSPEC® High Performance Mounted Machine Vision Filters are designed and manufactured for the most demanding machine vision and imaging applications. These filters pass or block specific UV, visible, or IR wavelengths and provide extremely wide angles of incidence. Compared to traditional filters, these hard coated filters provide superior blocking of unwanted light and greater durability for longer lifetimes. TECHSPEC® High Performance Mounted Machine Vision Filters can be used to improve image contrast and isolate spectral regions and colors. These filters are offered in a variety of colors and filter thread sizes.

Technical Information








Color Machine Vision Filters

Edmund Optics® TECHSPEC® High Performance Machine Vision Filters are designed with the industry's best performance to cost ratio in mind. With extremely sharp edge transition and flat peak transmission, users are guaranteed the optimal signal-to-noise ratio in their imaging system without losing light intensity that is critical for performance.

On average, the blocking range reaches far into the UV at 200nm and stretches out to 1200nm, which covers most of the noise and UV/IR signatures seen in conventional lamps and bulbs.

The graphs below demonstrate the performance typical to our Machine Vision Filters and other Hard Coated filters. The sharp cut-on and cut-off wavelengths are noticeably apparent, as well as transmission values that are >10% improved over traditional imaging filters on the market.



Filter Thread	Outer Diameter (mm)	Front Thread (to allow for stacking)	Filter Diameter (mm)	Thickness (mm)	Thread Length (mm)	Clear Aperture CA (mm)
M22.5 x 0.50	24.5	M22.5 x 0.50	20.1 ±0.1	4.5	2.0	18.5
M25.5 x 0.50	27.5	M25.5 x 0.50	23.0 ±0.1	4.5	2.0	21.5
M30.5 x 0.50	32.0	M30.5 x 0.50	28.0 ±0.1	5.0	2.0	26.5

M34.0 x0.50	36.0	M34.0 x0.50	31.6 ±0.1	5.0	1.5	30.0
M35.5 x0.50	37.0	M35.5 x0.50	33.1 ±0.1	5.0	2.0	31.5
M40.5 x0.50	42.0	M40.5 x0.50	38.0 ±0.1	5.0	2.0	36.5
M43.0 x0.75	45.0	M43.0 x0.75	40.2 ±0.1	5.0	2.0	39.2
M46.0 x0.75	48.0	M46.0 x0.75	43.2 ±0.1	4.8	2.2	41.5
M55.0 x0.75	57.0	M55.0 x0.75	52.2 ±0.1	4.8	2.2	50.5
M62.0 x0.75	65.0	M62.0 x0.75	59.2 ±0.1	5.5	2.5	57.5
