


[See all 66 Products in Family](#)

# SCHOTT NG9, 2.3 OD, 25mm Dia., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock #16-668 **20+ In Stock**

⊖ 1 ⊕ €44.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	€44,00 each
Qty 11-49	€38,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

### General

Neutral Density Filter **Type:**

### Physical & Mechanical Properties

25.00 **Diameter (mm):**

1.60 (nominal) **Thickness (mm):**

±0.38  
Dimensional Tolerance (mm):

## Optical Properties

Optical Density OD (Average):  
2.3 ± 0.07 @ 546nm

Class/Filter Number:  
**SCHOTT NG9**

Coating:  
Uncoated

Index of Refraction (n<sub>d</sub>):  
1.51

Surface Quality:  
80-50

Transmission (%):  
0.500 ± 0.085% @ 546nm

Wavelength Range (nm):  
400 - 700

## Material Properties

Transformation Temperature (°C):  
470

## Regulatory Compliance

Certificate of Conformance:  
[View](#)

Reach 240:  
**Compliant**

## Product Details

- Tightly Controlled Transmission Specifications
- NG4, NG9, or NG11 Glass Types
- Specified Optical Densities from 0.15 to 5.0
- Provide Even Light Attenuation in the Visible Spectrum
- **SCHOTT NG Gray Glass** Also Available



SCHOTT NG Absorptive Neutral Density (ND) Filters consist of NG4, NG9, or NG11 SCHOTT glass types and provide even light attenuation through absorption in the visible spectrum. These filters are manufactured to achieve a specified optical density, ranging from 0.15 to 5.0, to simplify integration into optical systems. SCHOTT NG Absorptive Neutral Density (ND) Filters are available in a standard 50 x 50mm size and multiple filters can be stacked to achieve custom optical densities. Custom sizes from 5 to 160mm as well as custom optical densities or transmission values for specific wavelengths are available on request; for more information, visit our [Colored Glass Filter Manufacturing](#) capabilities webpage. [SCHOTT NG Gray Glass Filters](#) are also available.

Each filter lot is measured and thickness is adjusted to meet the specified transmission value at 546nm. Variations in filter lot performance can result in variations in nominal thickness; however, the transmission variations between lots will be minimal.

## Filter Simulation Software

[Click here](#) to download SCHOTT's colored glass filter calculation program which can be used to calculate the internal transmittance and external transmission of each SCHOTT glass type. The program can simulate the performance of individual filters with user specified thickness or of stacked filters with varying glass types and thicknesses.

## Technical Information





**Quote Your Size**

**Compatible Mounts**

---