

[See all 21 Products in Family](#)

Oryx® ORX-10G-310S9M Mono 10GigE

See More by [Teledyne FLIR](#)



ORYX-10G-310S9C



Stock #20-254 **1 In Stock**

- 1 + €7.090⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€7.090,00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

Monochrome **Spectrum:**

General

Monochrome Camera **Type:**

ORX-10G-310S9M **Model Number:**

FLIR **Manufacturer:**

Oryx® **Camera Series:**

Physical & Mechanical Properties

60 x 60 x 115 **Dimensions (mm):**

508 **Weight (g):**

Full **Housing:**

Sensor

240MB **Image Buffer:**

APS-C **Sensor Format:**

31.00 **Resolution (Megapixels):**

26.00 **Frame Rate (fps):**

6,464 x 4,852 **Pixels (H x V):**

3.45 x 3.45 **Pixel Size, H x V (µm):**

22.30 x 16.74 **Sensing Area, H x V (mm):**

Sony IMX342 **Imaging Sensor:**

Progressive Scan CMOS **Type of Sensor:**

Global **Shutter Type:**

8/10/12 Bit **Pixel Depth:**

39µs - 30s **Exposure Time:**

67.17 **Dynamic Range (dB):**

GigE Vision **Machine Vision Standard:**

Electrical

13.9 **Power Consumption (W):**

Hardware & Interface Connectivity

10GigE **Interface:**

GigE interface with Screw Locks **Connector:**

Power Supply:
 Power Supply Required and Sold Separately:
 USA: [#19-803](#)
 Europe: [#19-803](#)
 Japan: [#19-803](#)
 Korea: Not Available
 China: [#19-803](#)

GPIOs:
 1 opto-isolated input, 1 opto-isolated output, 2 non-

isolated bi-directional

Synchronization:

Hardware Trigger (GPIO) or Software Trigger

Interface Port Orientation:

Back Panel

GPIO Connector Type:

12-pin Hirose (HR10)

Threading & Mounting

Mount:

F-Mount (With [#20-256](#))

Mounting Threads:

Built-in 1/4-20 Tripod Mount Adapter

Environmental & Durability Factors

Operating Temperature (°C):

0 to +50

Storage Temperature (°C):

-30 to +60

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- 10GBASE-T (10GigE) Ethernet Interface
- 3.2 to 31 Megapixel Sony 4th Gen Pregius S Sensors
- Supports 4K60, 12-bit System Integration
- Tripod Adapter Built into Larger Oryx® Models



Teledyne
Authorized
Distributor

Teledyne FLIR IIS Oryx 10GigE: High throughput, Award-winning camera designs

Reliably capture images at high speed

The **Oryx 10GigE** camera family supports transfer speeds of up to 10 Gbit/s enabling capture of 4K resolution, 12-bit images at speeds exceeding 60 FPS. Reliable image transfer at high bandwidth is further improved with Myricom bundles and packet resend feature. A range of sensor options offer resolutions from 3.2 Megapixel up to 31 Megapixel. Oryx features include IEEE1588 clock synchronization and full compatibility with several popular third-party software supporting GigE Vision. Oryx's 10GBASE-T interface is a proven and widely deployed standard that provides reliable image transfer at cable lengths over 50 meters on inexpensive CAT6A, and up to 30 meters on CAT5e.

Note: The ORX-10G-310S9 and ORX-10G-245S8 cameras require an F-Mount lens adapter (sold separately).

Features

- Color or monochrome sensors
- Various frame triggering options including up to 8 sets of 2-feature sequencer
- Pixel binning, decimation, ROI
- On camera image processing includes Gamma, LUT, and sharpness

Applications

- Stadium venues
- Site security
- Factory automation
- Traffic monitoring
- Inspection systems