

SWIR Inline Tube Lens



SWIR Inline Tube Lens

Stock **#26-223** **1 In Stock**

-

1

+

€6.210⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€6.210,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

Optical Properties	
1X	Magnification:
900 - 1700	Wavelength Range (nm):
Sensor	
1.1"	Maximum Sensor Format:
Threading & Mounting	

C-Mount	Mount:
M26	Mounting Threads:

Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- High-Resolution for Short Wave Infrared (SWIR) Wavelengths up to 1600nm
- Available in Magnifications of 1x to 50X
- Ideal for Photo Emission Detection, Laser Marking, and Laser Cutting

SWIR Plan APO Infinity Corrected Objectives are high resolution objective lenses with long working distances that are color corrected between 800 – 1600nm. Available in magnifications of 1X to 50X, these objectives feature high numerical apertures for high resolution imaging at SWIR wavelengths. With a common 95mm parfocal length, these objectives can be combined with a 200mm focal length tube lens and a compatible [C-mount camera](#) for easy system integration. SWIR Plan APO Infinity Corrected Objectives are ideal for Photo Emission Detection, Wafer Backside Inspection, Laser Glass Cutting, and Laser Scan Microscopy applications.