

- Manufacturing ▾
- Learn
- Company ▾

• **Shop**

English EUR
Shop by Category

- **Optics**
 - [Back](#)
 - [View All Optics](#)
 - **Optical Lenses**
 - [View All](#)
 - [Achromatic Lenses](#)
 - [Aspheric Lenses](#)
 - [Plano-Convex \(PCX\) Lenses](#)
 - [Double-Convex \(DCX\) Lenses](#)
 - [Plano-Concave \(PCV\) Lenses](#)
 - [Double-Concave \(DCV\) Lenses](#)
 - [Cylinder Lenses](#)
 - [Laser Lenses](#)
 - [Infrared \(IR\) Lenses](#)
 - [UV Lenses](#)
 - [Ball and Condenser Lenses](#)
 - [Fresnel Lenses](#)
 - [Focus Tunable Lenses](#)
 - [Light Pipes and Homogenizing Rods](#)
 - [Specialty Lenses](#)
 - [Lens Kits](#)
 - **Optical Mirrors**
 - [View All](#)
 - [Flat Mirrors](#)
 - [Off-Axis Mirrors](#)
 - [Nd:YAG Laser Mirrors](#)
 - [Broadband Dielectric Mirrors](#)
 - [Laser Line Mirrors](#)
 - [Ultrafast Laser Mirrors](#)
 - [Focusing \(Concave\) Mirrors](#)
 - [IR Mirrors](#)
 - [Hot and Cold Mirrors](#)
 - [Specialty Mirrors](#)
 - **Windows and Diffusers**
 - [View All](#)
 - [Visible Windows](#)
 - [UV and IR Windows](#)
 - [Laser Windows](#)
 - [Interferometry Windows](#)
 - [Specialty Windows](#)
 - [Optical Diffusers](#)
 - **Optical Filters**
 - [View All](#)
 - [Bandpass Filters](#)
 - [Longpass Filters](#)
 - [Shortpass Filters](#)
 - [Notch Filters](#)
 - [Neutral Density \(ND\) Filters](#)
 - [Color and Absorptive Filters](#)
 - [Dichroic Filters](#)
 - [Machine Vision Filters](#)
 - [Fluorescence Filters](#)
 - **Polarization Optics**
 - [View All](#)
 - [Linear Polarizers](#)
 - [Circular Polarizers](#)
 - [Depolarizers](#)
 - [Retarders \(Waveplates\)](#)
 - [Polarizing Beamsplitters](#)
 - [Polarization Testing](#)
 - [Optomechanics for Polarizers](#)
 - **Beamsplitters**
 - [View All](#)
 - [Plate Beamsplitters](#)
 - [Cube Beamsplitters](#)
 - [Polarizing Beamsplitters](#)
 - [Non-Polarizing Beamsplitters](#)
 - [Laser Beamsplitters](#)
 - **Prisms**
 - [View All](#)
 - [Right Angle Prisms](#)
 - [Dispersion Prisms](#)
 - [Penta Prisms](#)
 - [Image Rotation Prisms](#)
 - [Light Pipes and Homogenizing Rods](#)
 - [Mounted Prisms](#)
 - [Retroreflection Prisms](#)
 - [Specialty Prisms](#)
 - **Diffraction Gratings**
 - [View All](#)
 - [Ruled Reflective Diffraction Gratings](#)
 - [Holographic Reflective Diffraction Gratings](#)
 - [Echelle Reflective Gratings](#)
 - [Concave Diffraction Gratings](#)
 - [Transmissive Diffraction Gratings](#)
 - [Specialty Gratings](#)
 - **Optical Assemblies**
 - [View All](#)
 - [Optical Kits](#)
 - [C-Mount Optical Components](#)
 - [Laser Optic Assemblies](#)
 - [Alignment and Testing Accessories](#)
 - **SCHOTT Optical Components**
 - **Infrared Optics**
 - [View All](#)
 - [Germanium Optics](#)
 - [Zinc Selenide \(ZnSe\) Optics](#)
 - [Reflective IR Optics](#)
 - [Sapphire Optics](#)
 - [Silicon Optics](#)
 - [Calcium Fluoride Optics](#)
 - [Fused Silica Optics](#)
 - [Magnesium Fluoride Optics](#)
 - [Zinc Sulfide Optics](#)
 - [Chalcogenides](#)
 - [Other IR Materials](#)
 - [IR Assemblies](#)
 - **Fiber Optics**
 - **Laser Optics**
 - [View All](#)
 - [Laser Mirrors](#)
 - [Laser Lenses](#)
 - [Laser Windows](#)
 - [Laser Filters](#)
 - [Ultrafast Optics](#)
 - [Laser Beam Expanders](#)

- Laser Optical Assemblies
 - Laser Beam Shaping
 - Laser Beamsplitters
 - Laser Microscopy
 - Crystals and Isolators
 - Laser Polarization
 - Laser Prisms
 - New Laser Optics
- Ultrafast Optics
 - View All
 - Ultrafast Pulse Compression Mirrors
 - Low GDD Ultrafast Mirrors
 - Ultrafast Polarizers
 - Ultrafast Lenses and Windows
 - Ultrafast Optical Filters
 - Ultrafast Harmonic Separators and Beamsplitters
 - Ultrafast Laser Diagnostics
 - Reflective Objectives and Beam Expanders
 - Compression Prisms
 - Pulse Compression Gratings
 - Nonlinear Crystals
- IBS (Ion Beam Sputtering) Coated Optics
- Diffractive Optical Elements (DOE)
- New Optics
- Laser Optics
 - [Back](#)
 - [View All Laser Optics](#)
 - Laser Mirrors
 - View All
 - Laser Line Mirrors
 - Broadband Laser Mirrors
 - Ultrafast Laser Mirrors
 - Dichroic Mirrors & Harmonic Separators
 - Laser Mirror Substrates
 - Laser Lenses
 - View All
 - Plano-Convex (PCX) Laser Lenses
 - Aspheric Laser Lenses
 - Cylinder Laser Lenses
 - Laser Focusing Assemblies
 - Specialty Laser Lenses
 - Laser Windows
 - View All
 - Laser Line Windows
 - Broadband Laser Windows
 - Single Surface Coated Laser Windows
 - Uncoated Laser Windows
 - Specialty Laser Windows
 - Laser Filters
 - View All
 - Bandpass Laser Filters
 - Longpass Edge and Dichroic Laser Filters
 - Shortpass Edge and Dichroic Laser Filters
 - Notch Laser Filters
 - Harmonic Separators
 - Neutral Density (ND) Laser Filters
 - Ultrafast Optics
 - View All
 - Ultrafast Pulse Compression Mirrors
 - Low GDD Ultrafast Mirrors
 - Ultrafast Polarizers
 - Ultrafast Lenses and Windows
 - Ultrafast Optical Filters
 - Ultrafast Harmonic Separators and Beamsplitters
 - Ultrafast Laser Diagnostics
 - Reflective Objectives and Beam Expanders
 - Compression Prisms
 - Pulse Compression Gratings
 - Nonlinear Crystals
 - Laser Beam Expanders
 - View All
 - Scorpii® Beam Expanders
 - Vega® Beam Expanders
 - Arcturus® Beam Expanders
 - Draconis® Beam Expanders
 - Canopus® Beam Expanders
 - Variable Beam Expanders
 - CO₂ Beam Expanders
 - Jenoptik Beam Expanders
 - Laser Optical Assemblies
 - View All
 - Laser Beam Expanders
 - Pockels Cells
 - Focusing Objectives
 - Beam Shapers
 - Optical Isolators
 - F-Theta Lenses
 - Galvanometers
 - Laser Beam Shaping
 - Laser Beamsplitters
 - Laser Microscopy
 - Crystals and Isolators
 - Laser Polarization
 - Laser Prisms
 - New Laser Optics
- Optomechanics
 - [Back](#)
 - [View All Optomechanics](#)
 - Tube System
 - View All
 - Multi-Element Tube System
 - C, S, and T-Mount Components
 - SM Tube System
 - Optical Cage System
 - View All
 - Cage System Optical Mounts
 - Cage System Plates
 - Cage System Spheres
 - Cage System Accessories
 - Cage System Kits
 - Benchtop Optical Mounts
 - View All
 - E-Series Kinematic Optical Mounts
 - Optical Mirror Mounts
 - Optical Lens and Filter Mounts
 - Prism and Beamsplitter Mounts
 - Polarizer Mounts
 - Laser and Fiber Optic Mounts
 - Benchtop System
 - View All
 - Optical Posts
 - Optical Post Holders and Mounting Bases
 - Optical Post Accessories
 - Imaging Mechanics
 - Benchtop Brackets and Plates
 - Optical Tables and Breadboards

- View All
 - Bench Plates
 - Composite Breadboards
 - Vibration Isolation Tables
 - Optical Breadboard Accessories
- Motorized Stages
 - View All
 - Motorized Linear Translation Stages
 - Motorized Vacuum Stages
 - Motorized Rotary Stages
 - Motorized Linear Translation Actuators
 - Motorized Stages for Life Sciences
 - Piezo Driven Motorized Stages
 - Controllers for Motorized Stages
 - Accessories for Motorized Stages
- Manual Stages and Slides
 - View All
 - Stages and Slides
 - Accessories for Manual Stages and Slides
- Irises and Apertures
 - View All
 - Iris Diaphragms
 - Pinholes and Slits
 - Iris and Aperture Mounts
 - Shutters
- Accessories
 - View All
 - Tools
 - Thread Adapters and Screws
 - Plates and Brackets
 - Others
- New Optomechanics
- Microscopy
 - Back
 - **View All Microscopy**
 - Edmund Optics® Objectives
 - View All
 - Reflective Objectives
 - TECHSPEC® Objectives
 - Edmund Optics® 120i Plan APO Infinity Corrected Objectives
 - Mitutoyo Objectives
 - Olympus Objectives
 - Nikon Objectives
 - ZEISS Objectives
 - Automated Upright Microscopes
 - Infinity Corrected Objectives
 - Finite Conjugate Objectives
 - Reflective Objectives
 - TECHSPEC® Objectives
 - View All
 - TECHSPEC® Objectives
 - Microscopy Cameras
 - Microscopy Lighting
 - View All
 - Microscopy Illumination Sources
 - Fiber Optic Illuminators
 - Fiber Optic Light Guides
 - Microscopy Lighting Accessories
 - Microscope Systems
 - Microscopy Filters
 - View All
 - Microscopy Bandpass Filters
 - Microscopy Longpass and Dichroic Edge Filters
 - Microscopy Shortpass Edge Filters
 - Microscopy Neutral Density (ND) Filters
 - Modular Zoom Lenses
 - Microscopy Targets
 - Reticles and Stage Micrometers
 - Microscopy Mechanics
 - View All
 - C, S, and T-Mount Components
 - Optical Breadboard Components and Laboratory Tables
 - Posts and Post Holders
 - Optical Mounts
 - Linear Positioning Stages
 - Eyepieces
 - Relay Lenses and Couplers
 - Pocket and Direct Microscopes
 - Magnifiers
 - View All
 - Comparators
 - Contact Reticles
 - Handheld Magnifiers
 - Linen Testers
 - New Microscopy
- Lasers
 - Back
 - **View All Lasers**
 - Laser Sources
 - View All
 - Machine Vision Lasers
 - Life Science Lasers
 - Metrology Lasers
 - Gas Lasers
 - Industrial and Pointing Lasers
 - Material Processing Lasers
 - Laser Measurement and Electronics
 - View All
 - Laser Beam Analysis
 - Laser Power Meters
 - EO Laser Measurement
 - Infrared (IR) and Ultraviolet (UV) Viewers
 - Laser Electronics
 - Laser Optics
 - View All
 - Laser Mirrors
 - Laser Lenses
 - Laser Windows
 - Laser Filters
 - Ultrafast Optics
 - Laser Beam Expanders
 - Laser Optical Assemblies
 - Laser Beam Shaping
 - Laser Beamsplitters
 - Laser Microscopy
 - Crystals and Isolators
 - Laser Polarization
 - Laser Prisms
 - New Laser Optics
 - Optical Amplifiers
 - Laser Safety
 - View All
 - Laser Safety Glasses and Goggles
 - Laser Safety Windows
 - Laser Protection
 - Infrared (IR) and Ultraviolet (UV) Viewers

- Laser Mechanics
- Laser Accessories
- Lab and Production
 - View All
 - Optical Cleaning
 - Component Handling Tools
 - General Tools
 - Optical Adhesives
 - Acktar Blackened Products
 - Blackout Material
 - UV Lamps and Accessories
 - Storage
 - Lab Kits
 - Laser Safety
 - Magnets
- New Lasers
- Imaging Lenses
 - Back
 - **View All Imaging Lenses**
 - Fixed Focal Length Lenses
 - View All
 - Fixed Focal Length Lens Selector
 - Telecentric Lenses
 - M12 Lenses (S-Mount Lenses)
 - Zoom & Variable Magnification Lenses
 - View All
 - Zoom Lenses
 - Variable Magnification Lenses
 - High Magnification Long Working Distance Zoom Lenses
 - Microscope Objectives
 - View All
 - Infinity Corrected Objectives
 - Finite Conjugate Objectives
 - Reflective Objectives
 - Edmund Optics® Objectives
 - TECHSPEC® Objectives
 - Mitutoyo Objectives
 - Olympus Objectives
 - Nikon Objectives
 - ZEISS Objectives
 - Infinity Photo-Optical
 - Liquid Lenses
 - Ruggedized Lenses for Harsh Environments
 - Cinema Production and Advanced Photography
 - Imaging Lens Accessories
 - View All
 - Machine Vision Mounted Color Filters
 - Machine Vision Mounted UV-IR Filters
 - Machine Vision Mounted Polarizing Filters
 - Machine Vision Mounted Neutral Density (ND) Filters
 - Machine Vision Filter Kits
 - Filter Wheels
 - Threaded Filter Mounts
 - Filter Thread Adapters
- Cameras
 - Back
 - **View All Cameras**
 - USB Cameras
 - Gigabit Ethernet Cameras
 - Scientific Cameras
 - Teledyne FLIR Cameras
 - Teledyne Dalsa Cameras
 - Teledyne Lumenera Microscopy Cameras
 - Teledyne Photometrics Cameras
 - Allied Vision Cameras
 - Basler Cameras
 - IDS Imaging Cameras
 - LUCID Vision Labs Cameras
 - Pixelink® Cameras
 - JAI Cameras
 - 3D Cameras
 - View All
 - Stereo Cameras
 - Time of Flight (ToF) Cameras
 - Thermal Cameras
 - NIR Cameras
 - Camera Accessories and Optomechanics
 - Analog Cameras
 - FireWire Cameras
 - Imaging Systems
 - New Cameras
- Lights and Illumination
 - Back
 - **View All Lights and Illumination**
 - Machine Vision Lighting
 - View All
 - Ring Lights
 - Laser Light Source
 - Line Lights
 - Pattern Projectors
 - Bar Lights
 - Backlights
 - Inline Lights
 - Spot Lights
 - Diffuse Lights
 - Flat Dome Lights
 - Washdown Lights
 - Machine Vision Lighting Accessories
 - Microscopy Lighting
 - View All
 - Microscopy Illumination Sources
 - Fiber Optic Illuminators
 - Fiber Optic Light Guides
 - Microscopy Lighting Accessories
 - Spectroscopy Lighting
 - Laser Sources
 - View All
 - Machine Vision Lasers
 - Life Science Lasers
 - Metrology Lasers
 - Gas Lasers
 - Industrial and Pointing Lasers
 - Material Processing Lasers
 - Other Light Sources
 - Illumination Accessories
 - View All
 - Machine Vision Lighting Accessories
 - Microscopy Lighting Accessories
 - New Illumination
- Test Targets
 - Back
 - **View All Test Targets**
 - Resolution Test Targets
 - Distortion Test Targets
 - Image Analysis & Stage Micrometers
 - Color & Gray Level Test Targets

- USAF Targets
- Ronchi Rulings
- Reticles
- Testing and Detection
 - Back
 - [View All Testing and Detection](#)
 - Optical Metrology
 - Laser Measurement and Electronics
 - View All
 - Laser Beam Analysis
 - Laser Power Meters
 - EO Laser Measurement
 - Infrared (IR) and Ultraviolet (UV) Viewers
 - Laser Electronics
 - Detectors
 - Amplifiers
 - Light Meters
 - Spectroscopy
 - Scratch Dig and Roughness Standards
 - Measurement Tools
 - Active Optical Components
 - New Testing and Detection
- Lab and Production
 - Back
 - [View All Lab and Production](#)
 - Optical Cleaning
 - View All
 - Lens Tissue and Cloth
 - Optical Cleaning Kits
 - Gloves, Brushes, and Swabs
 - Lens Cleaners and Pouches
 - Optics Care Kit
 - Component Handling Tools
 - View All
 - Gloves
 - Pick-Up Tools
 - Tweezers and Pliers
 - Component Handling Kit
 - General Tools
 - Optical Adhesives
 - Acktar Blackened Products
 - Blackout Material
 - UV Lamps and Accessories
 - Storage
 - Lab Kits
 - Laser Safety
 - View All
 - Laser Safety Glasses and Goggles
 - Laser Safety Windows
 - Laser Protection
 - Infrared (IR) and Ultraviolet (UV) Viewers
 - Magnets
- Shop By Application
 - Back
 - [View All Shop By Application](#)
 - NIR Imaging
 - View All
 - VIS-NIR Imaging (400-1000 nm)
 - NIR Phosphor-Coated Silicon Imaging (1495-1595 nm)
 - SWIR Imaging
 - View All
 - SWIR Imaging Lenses
 - SWIR Illumination
 - SWIR Filters
 - Thermal Cameras
 - Computational Imaging
 - View All
 - Polarization Optics
 - Active Optical Components
 - Scientific Cameras
 - Galvanometers
 - E-Series Kinematic Optical Mounts
 - Diffractive Optical Elements (DOE)
 - Irises and Apertures
 - Diffraction Gratings
 - Specialty Lenses
 - Astronomical Imaging
 - View All
 - Image Rotation Prisms
 - Polarization Optics
 - Multiphoton Microscopy
 - View All
 - Optical Tables and Breadboards
 - Life Science Lasers
 - Low GDD Ultrafast Mirrors
 - Dichroic Filters
 - Galvanometers
 - Motorized Stages for Life Sciences
 - Infinity Corrected Objectives
 - Detectors
 - Cameras
 - Quantum Technologies
 - View All
 - Optical Isolators
 - XR | AR | MR
 - View All
 - Polarization Optics
 - Optical Adhesives
 - Specialty Windows
 - Optical Diffusers
 - M12 Lenses (S-Mount Lenses)
 - Test Targets
 - Testing and Detection
 - Diffractive Optical Elements (DOE)
 - Laser Material Processing
 - View All
 - Laser Beam Analysis
 - Material Processing Lasers
 - Laser Beam Expanders
 - Beam Steering & Scanning
 - F-Theta Lenses
 - Laser Power Meters
- Shop By Brand
 - Back
 - [View All Shop By Brand](#)
 - TECHSPEC®
 - View All
 - TECHSPEC® Objectives
 - Allied Vision
 - View All
 - Top Sellers from Allied Vision
 - More from Allied Vision
 - Coherent®
 - View All
 - Top Sellers from Coherent
 - More from Coherent

- Nikon
 - View All
 - Top Sellers from Nikon
 - Objective Lenses from Nikon
 - More from Nikon
- Olympus
 - View All
 - Top Sellers from Olympus
 - More from Olympus
- Teledyne
 - View All
 - Teledyne Dalsa Cameras
 - Teledyne FLIR Cameras
 - Teledyne Lumenera Microscopy Cameras
 - Teledyne Photometrics Cameras
- Aektar®
- AdlOptica
- Advanced Illumination
- Basler
- CCS
- Dolan-Jenner
- Everix
- Hoya
- IDS Imaging Development Systems
- Infinity Photo-Optical Company
- ISP Optics
 - View All
 - ISP Optics Infrared Lenses
 - ISP Optics Infrared Windows
 - ISP Optics Infrared Beamsplitters
 - ISP Optics Infrared Prisms
 - ISP Optics Infrared Mirrors
- Jenoptik
- Lightpath® Optical Components
- LUCID Vision Labs™
- Mitutoyo
- Norland
- Ocean Optics
- Optotune
- Richardson Gratings™
- ScannerMAX
- SCHOTT Optical Components
- TMC
- UltraFast Innovations (UFI)
- Zaber™
- ZEISS

- New Products

- Back
- [View All New Products](#)
- New Optics
- New Laser Optics
- New Optomechanics
- New Lasers
- New Microscopy
- New Imaging Lenses
- New Cameras
- New Illumination
- New Testing and Detection

- Clearance Products

- Back
- [View All Clearance Products](#)
- Clearance Laser Optics
- Clearance Optics
- Clearance Optomechanics
- Clearance Lasers
- Clearance Microscopy
- Clearance Imaging Lenses
- Clearance Cameras
- Clearance Illumination
- Clearance Test Targets
- Clearance Testing and Detection
- Clearance Lab and Production

- Recertified Products

- Back
- [View All Recertified Products](#)
- Recertified Optics
- Recertified Optomechanics
- Recertified Lasers
- Recertified Microscopy
- Recertified Imaging Lenses
- Recertified Cameras
- Recertified Illumination
- Recertified Lab and Production

- › Manufacturing

- › Knowledge Center





- › Edmund Events

- › Company

- › Product Tools and Discounts

- [Quick Quote Tool](#)
- [Custom Quoting & Calculators](#)
- [Product Selection Tools](#)
- [Programs & Promotions](#)

- › Help and My Account

-  [My Account](#)
-  [Contact Us and Help](#)
- 
- 

- ›

[See all 102 Products in Family](#)

IDS U3-3080CP-M-GL, USB 3.0, 2/3" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ USB3 Camera, CP Model (Front)



×

STOCK #16-517 3 In Stock

[Similar Cameras](#)

⊖ 1 ⊕

€1.610⁰⁰

×

Add to Cart

Volume Pricing	
Qty 1+	€1.610,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

- [Create an account or log in to access saved list](#)

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

Monochrome

Spectrum:

General

Monochrome Camera

Type:

U3-3080CP-M-GL

Model Number:

IDS Imaging Development Systems

Manufacturer:

uEye+ CP

Camera Series:

Physical & Mechanical Properties

Dimensions (mm):

29 x 29 x 29 (excludes connectors and lens mount)

50	Weight (g):
Full	Housing:
Sensor	
128MB	Image Buffer:
2/3"	Sensor Format:
5.01	Resolution (Megapixels):
77.00	Frame Rate (fps):
2,456 x 2,054	Pixels (H x V):
3.45 x 3.45	Pixel Size, H x V (µm):
8.473 x 7.086	Sensing Area, H x V (mm):
Sony IMX250	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
12 bit	Pixel Depth:
0.036ms - 2000ms	Exposure Time:
70.00	Dynamic Range (dB):
USB3 Vision	Machine Vision Standard:
Electrical	
1.6 - 3.7	Power Consumption (W):
Hardware & Interface Connectivity	
USB 3.0	Interface:
USB 3.0 micro-B, screwable	Connector:
Power over USB	Power Supply:
2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Output Supply Voltage, 1 Ground	GPIOs:
Hardware Trigger (GPIO)	Synchronization:
Back Panel	Interface Port Orientation:
8-pin Hirose connector (HR25-7TR-8PA(73))	GPIO Connector Type:
Threading & Mounting	
C-Mount	Mount:
1/4-20 with Tripod Mount Adapter #35-088	Mounting Threads:
Environmental & Durability Factors	
0 to +55	Operating Temperature (°C):
-20 to +60	Storage Temperature (°C):
Regulatory Compliance	
Exempt x	RoHS 2015:
View x	Certificate of Conformance:
Contains SVHC(s) x	REACH 241:

Product Details

- Standard (SE), Compact (CP), and Ultra Compact (XCP) Housing Options Available
- C-Mount with Large Format CMOS Sensors up to 1.1"
- Up to 20.44MP Resolution with Framrates up to 396fps

IDS Imaging uEye CP/XCP/SE USB3 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for easy software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The XCP cameras have an ultra-compact size of 29 x 29 x 17mm and are an excellent option for price-sensitive, single-camera applications. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat-sensitive applications. IDS Imaging uEye CP/XCP/SE USB3 Cameras are ideal for manufacturing, industrial, and automation applications.

□
;