



SCHOTT NG11, 50mm Sq., 2mm Thick, Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



SCHOTT NG Gray Glass Neutral Density (ND) Filters



Stock **#14-106** **14 In Stock**

-

1

+

€99ST

ADD TO CART

Volume Pricing	
Qty 1-10	€99,91 each
Qty 11-49	€87,55 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Neutral Density Filter	Type:
Physical & Mechanical Properties	
50.0 x 50.0	Dimensions (mm):
50.00	Length (mm):
2.00 ±0.2	Thickness (mm):
50.00	Width (mm):
≤3	Parallelism (arcmin):
±0.2	Dimensional Tolerance (mm):
Optical Properties	
0.25	Optical Density OD (Average):
SCHOTT NG11	Glass/Filter Number:
Uncoated	Coating:
1.52	Index of Refraction (n _d):
60-40	Surface Quality:
56	Transmission (%):
(nominal)	Transmission Tolerance (%):
(nominal)	Optical Density Tolerance (%):
Material Properties	
481	Transformation Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Tightly Controlled Thickness Specifications
- Standard Thicknesses of 1, 2, and 3mm
- Even Light Attenuation in the Visible Spectrum
- NG1, NG3, NG4, NG5, NG9 and NG11 Glass Types Available
- Precision SCHOTT NG Glass Filters Also Available

SCHOTT NG Gray Glass Neutral Density (ND) Filters feature nearly constant transmittance in the visible spectrum, attenuating light through absorption. The filters are available in 6 materials, each with a thickness of 1, 2, or 3mm. Filters can be stacked to achieve custom optical densities. SCHOTT NG Gray Glass Neutral Density (ND) Filters are used in a variety of machine vision, [factory automation](#), and analytical instrumentation applications. Custom sizes from 5 to 160mm are available upon request; for more information, visit our [Colored Glass Filter Manufacturing](#) capabilities webpage. [SCHOTT NG Absorptive Neutral Density \(ND\) Filters](#) with precision optical density and transmission values are also available.

While SCHOTT NG Gray Glass Neutral Density (ND) Filters will provide consistent transmission values from 400 - 700nm, variations in filter lot manufacturing may lead to variations in transmission from filter to filter. Please see the table in the Technical Information tab for acceptable transmission variations for each glass type and thickness.

Filter Simulation Software

[Click here](#) to download SCHOTT's colored glass filter calculation program which can be used to calculate the internal transmittance and external transmission of each SCHOTT glass type. The program can simulate the performance of individual filters with user specified thickness or of stacked filters with varying glass types and thicknesses.


Interactive transmission curves are also available [here](#).

Immediate Custom Quotes Available


If you have a need for anyround, square, or rectangular size of a SCHOTT NG Gray Glass Neutral Density (ND) Filter in dimensions between 5mm and 50mm, please visit our [Colored Filter Glass Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 2 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized filters to your requirements, visit our [Customized Optical Filter Glass Capabilities](#) page.

TECHNICAL INFORMATION

Schott NG Absorptive ND Filters (1mm Thickness) Visible Spectrum



Schott NG Absorptive ND Filters (1mm Thickness) Extended Spectrum



Glass Type	Thickness	Min. Transmission (%)	Max. Transmission (%)
NG3	1	7.4	11.1
	2	0.01	2.8
	3	0.01	1.9
NG4	1	24.9	31.3
	2	6.1	11.6
	3	0.01	5.5
NG5	1	49.8	55.4
	2	27.2	32.8
	3	14.3	19.9
NG9	1	1.8	5.5
	2	0.01	2.0
	3	0.01	1.8
NG11	1	70.1	73.8
	2	54.2	57.9
	3	42.2	45.9

QUOTE YOUR SIZE

COMPATIBLE MOUNTS
