

SWIR 1050nm Homogeneous Backlight



Efilux SWIR LED Backlights

Stock **#28-628** [CONTACT US](#)

⊖ 1 ⊕ €2.390⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€2.390,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Model Number:
EFFI-MBL-100T-100-1050P

Type of Illumination:
LED Illuminator

>90% **Uniformity (%):**

Efflux **Manufacturer:**

Backlight **Geometry:**

Continuous with AIC (Analog Intensity Control) **Illumination Mode:**

Physical & Mechanical Properties

136.5 x 109.5 x 80.0 **Dimensions (mm):**

100 x 100 **Active Area (mm):**

Optical Properties

SWR **Color:**

1,050.00 **Wavelength (nm):**

Hardware & Interface Connectivity

M12, 4 pins **Connector:**

24VDC **Input Voltage (V):**

Power Supply:
Power Supply Required and Sold Separately.
USA: [#15-874](#)
Europe: [#15-875](#)
Japan: [#73-409](#)
Korea: [#73-409](#)
China: [#15-874](#)

Environmental & Durability Factors

-20 to 70 **Operating Temperature (°C):**

IP50 **Environmental Rating:**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

PRODUCT DETAILS

- Full Range of SWIR Wavelengths Available
- High Intensity and Uniform Lighting
- Feature >80% Homogeneity at Design Wavelength

Efflux SWIR LED Backlights provide intense and uniform lighting for machine vision, sorting and silicon inspection applications. These are available in wavelengths of 1050, 1200, 1300, 1450, 1550, and 1650nm. The backlights are designed with >80% homogeneity at their design wavelengths. Efflux SWIR LED Backlights are ideal complements for applications utilizing TECHSPEC® C Series Fixed Focal Length SWIR Lenses, TECHSPEC® SilverTL™ SWIR Telecentric Lenses and LUCID Vision Labs Triton™ GigE Power over Ethernet (PoE) SWIR Cameras or Teledyne FLIR IIS Forge 1GigE SWIR Cameras.