

SWIR 1200nm Adjustable Bar Light



Effilux SWIR LED Bar Lights

Stock #28-617 [CONTACT US](#)

- 1 + €1.350⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€1.350,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Model Number:
EFFI-FLEX-5-1200-KIT-ELS-600-24V

Number of LEDs:
5

Type of Illumination:
LED Illuminator

Manufacturer:
Effilux

Geometry:

Bar Light

Strobed or Constant

Illumination Mode:

Physical & Mechanical Properties

51.0 W x 135.0 L x 49.0 H

Dimensions (mm):

360

Weight (g):

Optical Properties

SWIR

Color:

1,200

Wavelength (nm):

Hardware & Interface Connectivity

M12, 4 pins

Connector:

24V DC

Input Voltage (V):

Power Supply:

Power Supply Required and Sold Separately.

USA: [#15-874](#)

Europe: [#15-875](#)

Japan: [#73-409](#)

Korea: [#73-409](#)

China: [#15-874](#)

Threading & Mounting

2 Rails (1 for M6 T-Nuts)

Mount:

Environmental & Durability Factors

0 to 50

Operating Temperature (°C):

IP50

Environmental Rating:

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- Full Range of SWIR Wavelengths Available
- High Intensity and Uniform Lighting
- Adjustable Illumination Angles

Effilux SWIR LED Bar Lights provide intense and uniform lighting for machine vision, sorting and silicon inspection applications. Available in wavelengths of 1050, 1200, 1300, 1450, 1550, and 1650nm. These bar lights feature adjustable lens positions and illumination angles for added flexibility. Effilux SWIR LED Bar Lights are ideal complements for applications utilizing TECHSPEC® C Series Fixed Focal Length SWIR Lenses, TECHSPEC® SilverTL™ SWIR Telecentric Lenses and LUCID Vision Labs Triton™ GigE Power over Ethernet (PoE) SWIR Cameras or Teledyne FLIR IIS Forge 1GigE SWIR Cameras.

Note: Included with the bar lights are one semi diffuse window and one 25° lens position kit.

[3D-Printable Mount Files](#)



Bar or Line Light Configuration

[Download Now](#)

Designed for use with the [Articulating Arm Mounting Systems](#), these 3D-printed mounts allow easy positioning of lights in brightfield or darkfield setups. The design is based on mounting illumination to 1/4-20" breadboards or into 80/20 extrusion systems, but can be adapted based on user needs. Mounts are available for ring, bar, line, and inline spot lights.



[Application Note](#)

Illumination Mounts for Machine Vision Applications

[Read](#)



[Video](#)

Assembly of 3D Printed Mounts for Common Illumination Geometries

[Watch](#)