

[See all 12 Products in Family](#)

UV Solarization-Resistant Fiber Patch Cord, 600 µm Core, Silicone-coated steel monocoil

See More by [Ocean Optics](#)



Stock #90-556 **NEW** 1 In Stock

− 1 + €395⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1+ | €395,00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

QP600-2-SR **Model Number:**

Physical & Mechanical Properties

2 **Length (m):**

600 **Core Diameter (µm):**

Jacket Material:

Optical Properties

| | |
|------------|-------------------------------|
| 0.22 | Numerical Aperture NA: |
| 200 - 1100 | Wavelength Range (nm): |

Hardware & Interface Connectivity

| | |
|-----|-------------------|
| SMA | Connector: |
|-----|-------------------|

Material Properties

| | |
|-----------|-------------------------|
| Polyimide | Buffer Material: |
|-----------|-------------------------|

Regulatory Compliance

| | |
|---------------------------|-------------------|
| Compliant | RoHS 2015: |
|---------------------------|-------------------|

| | |
|----------------------|------------------------------------|
| View | Certificate of Conformance: |
|----------------------|------------------------------------|

| | |
|---------------------------|-------------------|
| Compliant | Reach 250: |
|---------------------------|-------------------|

Product Details

- Connects Directly with Ocean Optics Spectrometers & Accessories
- Broad Wavelength Coverage: VIS-NIR, SR, and XSR Fibers Optimized for 180–2100 nm
- Solarization-Resistant Fibers Maintain Signal Accuracy Under Harsh UV
- Multiple Jacketing Choices for Durability and Tight Bend Radius Needs

Ocean Optics offers a complete line of premium optical fiber patch cords compatible with [Ocean Optics spectrometers](#) to suit a range of VIS-NIR and UV-NIR spectroscopy needs. Use them as illumination or read fibers to connect spectrometers, light sources, probes, or sampling accessories with maximum transmission efficiency and minimal signal loss. Choose standard visible-NIR assemblies for broadband applications or select solarization-resistant options to maintain signal fidelity when working with high UV power. Ocean Optics Spectrometer Patch Cords are available with a range of jacketing options designed to enhance durability and accommodate applications requiring a tight bend radius.

VIS-NIR Patch Cords (400–2100 nm): Best for routine broadband spectroscopy with minimal OH content, minimizing light absorption caused by hydroxyl ions (OH⁻), for efficient NIR transmission.

Solarization-Resistant Patch Cords (200–1100 nm): Ideal for UV-NIR work where standard silica fibers degrade under high UV exposure.

Extreme Solarization-Resistant Patch Cords (180–800 nm): Essential for deep-UV applications where the highest UV resistance is required.