





+ 0.4861
x 0.5876
■ 0.6563



SURFACE: INH

DPA: 0.000 MM

SPOT DIAGRAM

62489INK
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 2.520
GD RADIUS : 4.732
SCALE BAR : 10


REFERENCE : CHIEF RAY

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

CHROMATIC FOCAL SHIFT

62489INK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 137.2493 μm
DIFFRACTION LIMITED RANGE: 84.783 μm
PUPIL ZONE: 0.0000

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)




TRANSVERSE RAY FAN PLOT

62489INK
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 20.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



POLYCHROMATIC DIFFRACTION MTF

62489INK
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm .
SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)