





63690
MON APR 27 2009 UNITS ARE μm .
FIELD : 1
RMS RADIUS : 6.749
CED RADIUS : 11.047
SCALE BAR : 40

REFERENCE : CHIEF RAY


EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

63690
MON APR 27 2009
MAXIMUM FOCAL SHIFT RANGE: 66.7282 μm
DIFFRACTION LIMITED RANGE: 6.254 μm
PUPIL ZONE: 0.0000

CHROMATIC FOCAL SHIFT



EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)



TRANSVERSE RAY FAN PLOT


63690
MON APR 27 2009
MAXIMUM SCALE: $\pm 20.000 \mu\text{m}$.
0.486 0.588 0.656

SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)

63690
MON APR 27 2009
DATA FOR 0.4000 TO 0.7000 μm .
SURFACE: IMAGE

POLYCHROMATIC DIFFRACTION MTF



EDMUND OPTICS
[HTTP://WWW.EDMUNDOPTICS.COM](http://www.edmundoptics.com)