



NOTES:

1. ALLOWABLE OPTICAL MATERIAL:
FUSED SILICA CORNING 7980
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 5 ARCMIN
3. COATING (APPLY ACROSS COATING APERTURE)
S1: NONE
S2: NONE

4. SIX SIDEWALLS:
SURFACE ACCURACY: COMMERCIAL POLISH



FOR INFORMATION ONLY:
DO NOT MANUFACTURE PARTS TO THIS DRAWING

	S1	S2				
SHAPE	PLANO	PLANO	EFL (AT 587.6nm)	NA	TITLE	8mm HEX LIGHT PIPE, 150mm lg
SURFACE ACCURACY AT 632.8nm	2 WAVES	2 WAVES	BFL (AT 587.6nm)	NA	DWG NO	65837
SURFACE QUALITY	60 - 40	60 - 40	ALL DIMS IN	mm		

EO[®] Edmund Optics[®]