





NOTES:

- 1. SUBSTRATE:
ND Filter Glass
- 2. OPTICAL DENSITY: 0.3
- 3. COATING SPECIFICATION:
AR Coating: MgF2
R(AVG) ≤1.75% @ 400 - 700nm
- 4. TRANSMISSION (%): 50
- 5. FILTER THREAD: M37 x 0.75

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



SECTION A-A



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



			THIRD ANGLE PROJECTION 		TITLE	FILTER ND MTD 0.3OD 37X0.75		
SHAPE	S1 PLANO	S2 PLANO	ALL DIMS IN	mm	DWG NO	59165		SHEET 1 OF 1
SURFACE QUALITY	80-50	80-50						