





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**




LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CUT-ON WAVELENGTH	900nm
TRANSMISSION WAVELENGTH	935 - 2000nm
REJECTION WAVELENGTH	675 - 855nm
TRANSMISSION	>85
SURFACE QUALITY	40-20
COATING TYPE	TRADITIONAL COATED



THIRD ANGLE PROJECTION 		TITLE	M30.5 x 0.5, 900nm MOUNTED LONGPASS FILTER	
ALL DIMS IN	mm	DWG NO	66694	SHEET 1 OF 1