




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



| REV. A | VALUE |
|-------------------------|----------------------|
| SHAPE | PLANO |
| TRANSMISSION WAVELENGTH | 488 - 647.1 |
| DURABILITY | MIL-C-48497A |
| CUT-ON WAVELENGTH | 480 |
| SURFACE FLATNESS | >95 |
| SURFACE QUALITY | 60-40 |
| CLEAR APERTURE | Ø45.3 |
| BEVEL | PROTECTIVE AS NEEDED |

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**



THIRD ANGLE
PROJECTION

TITLE

Ø50mm, 480nm, DICHROIC LASER BEAM
COMBINER

ALL DIMS IN

mm

DWG NO

86398

SHEET
1 OF 1