





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CENTER WAVELENGTH (CWL)	808nm
FULL WIDTH HALF MAX (FWHM)	3 ± 1.0nm
MINIMUM TRANSMISSION	>80%
BLOCKING WAVELENGTH RANGE	650 - 800 & 816 - 1100nm
SURFACE QUALITY	60-40
COATING TYPE	HARD COATED



ALL DIMS IN

mm

EO® **Edmund Optics®**

TITLE

Ø12.5mm, 808nm CWL, 3nm FWHM, HARD
COATED LASER CLEAN-UP FILTER

DWG NO

68854

SHEET
1 OF 1