





**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CENTER WAVELENGTH (CWL)	632.8nm
FULL WIDTH HALF MAX (FWHM)	3 ±1.0nm
MINIMUM TRANSMISSION	>80%
BLOCKING WAVELENGTH RANGE	500 - 627 & 639 - 900nm
SURFACE QUALITY	60-40
COATING TYPE	HARD COATED

THIRD ANGLE  
PROJECTION

ALL DIMS IN

mm

Edmund Optics®

TITLE

Ø25mm, 632.8nm CWL, 3nm FWHM, HARD COATED LASER CLEAN-UP FILTER

DWG NO

68879

SHEET

1 OF 1