





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CENTER WAVELENGTH (CWL)	785nm
FULL WIDTH HALF MAX (FWHM)	3 ±1.0nm
MINIMUM TRANSMISSION	>80%
BLOCKING WAVELENGTH RANGE	650 - 777 & 793 - 1100nm
SURFACE QUALITY	60-40
COATING TYPE	HARD COATED



ALL DIMS IN

mm

EO[®] Edmund Optics[®]

TITLE

Ø50mm, 785nm CWL, 3nm FWHM, HARD
COATED LASER CLEAN-UP FILTER

DWG NO

68916

SHEET
1 OF 1