





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



BANDPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
CENTER WAVELENGTH (CWL)	1064nm
FULL WIDTH HALF MAX (FWHM)	$5 \pm 1.5\text{nm}$
MINIMUM TRANSMISSION	>80%
BLOCKING WAVELENGTH RANGE	900 - 1054 & 1074 - 1400nm
SURFACE QUALITY	60-40
COATING TYPE	HARD COATED



ALL DIMS IN mm

EO[®] Edmund Optics[®]

TITLE

$\varnothing 50\text{mm}$, 1064nm CWL, 5nm FWHM, HARD
COATED LASER CLEAN-UP FILTER

DWG NO

68923

SHEET
1 OF 1