


NOTES:

- 1. SUBSTRATE:
N-BK7
- 2. COATING (APPLY ACROSS COATING APERTURE)
S1: ALUMINUM COATED W/ PROTECTIVE OVERCOAT
R(AVG)>85% FROM 400-700nm, @ 45° AOI

S2: NONE
3. FINE GRIND SURFACE

- 4. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	<div><div>THIRD ANGLE PROJECTION</div><div></div><div>TITLE</div><div>45mm, Aluminum Coated, N-BK7 Right Angle Prism</div></div>			
SHAPE	PLANO	PLANO				
SURFACE QUALITY	60-40	60-40	ALL DIMS INmm			
CLEAR APERTURE	57.24 x 40.5	40.5 x 40.5				
COATING APERTURE	57.24 x 40.5	40.5 x 40.5	DWG NO32534			
SURFACE FLATNESS	λ/4	λ/4				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	SHEET1 OF 1			