

NOTES:


- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH \$1 TO <1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: RAVG ≤0.4% @ 425 - 675nm



5. Rohs Compliant







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
CLEAR APERTURE	Ø11.25	Ø11.25
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

	1 .	
THIRD ANGLE PROJECTION	\bigcirc	TIT
	I	
ALL DIMS IN	mm	D۷

B	Edmund Optics®
LE	12.5mm DIA., 3mm THICK, VIS 0° COATED λ/4 N-BK7 WINDOW

 DIMS IN
 mm
 DWG NO
 47517
 SHEET 1 OF 1