




NOTES:

- 1. SUBSTRATE:
BOROFLOAT®
- 2. COATING SPECIFICATION:
S1: Protected Aluminum (400-2000nm)
R(AVG) >85% @ 400 - 700nm
R(AVG) >90% @ 400 - 2000nm



3. FINE GROUND SURFACE

- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | | | | | | |
|-----------------|--|----------------------|----------------------|--|-------|--|
| | | S1 | S2 |  Edmund Optics® | | |
| SHAPE | | PLANO | PLANO | THIRD ANGLE PROJECTION  | TITLE | 22 x 22mm Protected Aluminum, λ/4 Mirror |
| SURFACE QUALITY | | 60-40 | GROUND | | | |
| CLEAR APERTURE | | 18.70 X 18.70 | N/A | | | |
| BEVEL | | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED | ALL DIMS IN | mm | DWG NO 33510 |
| | | | | | | SHEET 1 OF 1 |