NOTES:

1. SUBSTRATE MATERIAL: FLOAT GLASS


2. ROHS COMPLIANT


3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 75% R ±5% @ 550nm 25% T ±5% @ 550nm

S2: NONE

EDGES CUT





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

1 OF 1

REV. A	\$1	\$2			
SHAPE	PLANO	PLANO			
SURFACE QUALITY	80-50	80-50			
SURFACE FLATNESS	4 - 6λ	4 - 6λ			
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED			

			Edmund Optic	S®
HIRD ANGLE ROJECTION	$\phi \Leftrightarrow$	TITLE	25 x 38mm, 75 R/25 T, PLATE BEAMSPLI	ITER
all DIMS IN	mm	DWG NO	31435	SHEET 1 OF