



NOTES:

1. SUBSTRATE MATERIAL:
N-BK7
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: VIS 0°



R(avg) ≤0.4% @ 425 - 675nm

3. FINE GROUND SURFACE
4. POWER, IRREGULARITY, AND SURFACE QUALITY
SPECIFICAIONS APPLY ACROSS CLEAR APERTURE
5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2	 Edmund Optics®								
SHAPE	CONVEX	PLANO									
RADIUS	15.5	∞	EFL	30		TITLE	10mm DIA X 30mm FL VIS 0° COATED, CYLINDER LENS				
SURFACE QUALITY	60-40	60-40	BFL	28.67							
CLEAR APERTURE	Ø9.00	Ø9.00	ALL DIMS IN		mm		DWG NO	69697			SHEET 1 OF 1
COATING APERTURE	Ø9.00	Ø9.00									
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED									