



NOTES:

1. SUBSTRATE MATERIAL:
Fused Silica
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Protected Silver
R(avg) >98% @ 450 - 2000nm
R(avg) >98% @ 2000 - 10,000nm
S2: NONE



3. FINE GROUND SURFACE

4. PARALLELISM: 30 ARCSEC
5. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2				
SHAPE	PLANO	PLANO				
SURFACE QUALITY	20-10	N/A				
SURFACE FLATNESS	λ/10	COMMERICAL POLISH	TITLE75mm Square Silver Coated, λ/10 Mirror			
CLEAR APERTURE	90%	N/A				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO84446	SHEET1 OF 1